










PART NUMBER SEE SHEET 2



spec ref		*		dr		Xie Bob		2014/01/21		projection				size		A3		scale		3:2			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Rainbow Zhan		2014/06/19						ecn no		-							
ASME Y14.5				chr		Li-He		2014/06/19						rel level		Released							
				appr		Pei-Ming Zheng		2014/06/19						product family		PwrBlade+							
surface				linear		0.X		±0.5				title		8P + 72S + 8P		dwg no		10106129-G018001		rev		A	
				0.XX		±0.25																	
				0.XXX		±0.10																	
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw		sheet 1 of 3									

A

B

C

D


A

B

C

D

- NOTES:
- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



dr	Xie Bob	2014/01/21	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2	
eng	Rainbow Zhan	2014/06/19			ecn no	-			
chr	Li- He	2014/06/19							
appr	Pei-Ming Zheng	2014/06/19	product family		PwrBlade+	rel level	Released		
	title	8P + 72S + 8P VERTICAL PF HEADER			dwg no	10106129-G018001		rev A	
www.fci.com	cat. no.	Product - Customer Drw				sheet 3 of 3			