Part Number : 1200650414
Product Description : M12 Signal, A-Coded, Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 2.0m (6.56') Length
Series Number : 120065
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 804006A09M020



Documents and Resources

Drawings

1200650414_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120065
Description	M12 Signal, A-Coded, Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Single Ended
UPC	78678824120

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.10mm (.201")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail

Downloaded from Arrow.com.

Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

Downloaded from Arrow.com.