

## SERIES: SWI6-N | DESCRIPTION: AC-DC POWER SUPPLY

### FEATURES


- up to 6 W continuous power
- DoE Level VI efficiency
- no load power consumption < 0.1 W
- compact size
- universal input voltage range
- over voltage, over current, and short circuit protections
- UL/cUL safety approvals
- certified to 60950-1 and 62368-1 standards



| MODEL      | output voltage<br>(Vdc) | output current<br>max<br>(A) | output power<br>max<br>(W) | ripple and noise <sup>1</sup><br>max<br>(mVp-p) | efficiency level |
|------------|-------------------------|------------------------------|----------------------------|-------------------------------------------------|------------------|
| SWI6-3.3-N | 3.3                     | 1.5                          | 4.95                       | 100                                             | VI               |
| SWI6-5-N   | 5.0                     | 1.5                          | 7.5                        | 100                                             | VI               |
| SWI6-5.9-N | 5.9                     | 1.2                          | 7.08                       | 100                                             | VI               |
| SWI6-7.5-N | 7.5                     | 1.0                          | 7.5                        | 100                                             | VI               |
| SWI6-9-N   | 9.0                     | 0.67                         | 6.03                       | 100                                             | VI               |
| SWI6-12-N  | 12.0                    | 0.6                          | 7.2                        | 120                                             | VI               |
| SWI6-15-N  | 15.0                    | 0.5                          | 7.5                        | 150                                             | VI               |

Notes: 1. At full load, nominal input, 20 MHz bandwidth oscilloscope, output terminated with 0.1  $\mu$ F multilayer ceramic and 47  $\mu$ F low ESR electrolytic capacitors.

### PART NUMBER KEY



## INPUT

| parameter                 | conditions/description                  | min | typ     | max  | units |
|---------------------------|-----------------------------------------|-----|---------|------|-------|
| voltage                   |                                         | 90  | 100~240 | 264  | Vac   |
| frequency                 |                                         | 47  | 50~60   | 63   | Hz    |
| current                   |                                         |     |         | 0.19 | A     |
| inrush current            | at 240 Vac, full load, 25°C, cold start |     |         | 60   | A     |
| leakage current           |                                         |     |         | 0.25 | mA    |
| no load power consumption | at 115/230 Vac                          |     |         | 0.1  | W     |

## OUTPUT

| parameter    | conditions/description                   | min | typ       | max | units  |
|--------------|------------------------------------------|-----|-----------|-----|--------|
| regulation   | 3.3 Vdc output model<br>all other models |     | ±10<br>±5 |     | %<br>% |
| hold-up time | at full load                             | 10  |           |     | ms     |

## PROTECTIONS

| parameter                | conditions/description          | min | typ | max | units |
|--------------------------|---------------------------------|-----|-----|-----|-------|
| over voltage protection  | output shut down                |     |     | 180 | %     |
| over current protection  | output shut down, auto recovery |     |     |     |       |
|                          | 3.3 Vdc output model            |     |     | 3.5 | A     |
|                          | 5 Vdc output model              |     |     | 3.5 | A     |
|                          | 5.9 Vdc output model            |     |     | 3.0 | A     |
|                          | 7.5 Vdc output model            |     |     | 2.5 | A     |
|                          | 9 Vdc output model              |     |     | 1.5 | A     |
|                          | 12 Vdc output model             |     |     | 1.5 | A     |
|                          | 15 Vdc output model             |     |     | 1.3 | A     |
| short circuit protection | output shut down, auto recovery |     |     |     |       |

## SAFETY & COMPLIANCE

| parameter            | conditions/description                               | min     | typ   | max | units |
|----------------------|------------------------------------------------------|---------|-------|-----|-------|
| isolation voltage    | input to output at 10 mA for 1 minute                |         | 3,000 |     | Vac   |
| isolation resistance | input to output at 500 Vdc                           | 10      |       |     | MΩ    |
| safety approvals     | certified to 60950-1: UL<br>certified to 62368-1: UL |         |       |     |       |
| EMI/EMC              | FCC Part 15B Class B                                 |         |       |     |       |
| MTBF                 | as per Telcordia SR-332, 25°C                        | 300,000 |       |     | hours |
| RoHS                 | yes                                                  |         |       |     |       |

## ENVIRONMENTAL


| parameter             | conditions/description | min | typ | max | units |
|-----------------------|------------------------|-----|-----|-----|-------|
| operating temperature |                        | 0   |     | 40  | °C    |
| storage temperature   |                        | -20 |     | 60  | °C    |
| operating humidity    | non-condensing         | 20  |     | 80  | %     |
| storage humidity      | non-condensing         | 10  |     | 90  | %     |

MECHANICAL

| parameter  | conditions/description | min | typ | max | units |
|------------|------------------------|-----|-----|-----|-------|
| dimensions | 56 x 28 x 42           |     |     |     | mm    |
| inlet plug | North America, 2-pin   |     |     |     |       |
| weight     |                        |     | 78  |     | g     |

MECHANICAL DRAWING

units: mm  
tolerance: ±1.0 mm



DC CORD

units: mm




Table 1

| MODEL NO.  | CABLE          | CORD LENGTH  |
|------------|----------------|--------------|
| SWI6-3.3-N | UL2468, 20 AWG | 1,500 mm ±30 |
| SWI6-5-N   | UL2468, 20 AWG | 1,500 mm ±30 |
| SWI6-5.9-N | UL2468, 20 AWG | 1,500 mm ±30 |
| SWI6-7.5-N | UL2468, 22 AWG | 1,500 mm ±30 |
| SWI6-9-N   | UL2468, 22 AWG | 1,500 mm ±30 |
| SWI6-12-N  | UL2468, 22 AWG | 1,500 mm ±30 |
| SWI6-15-N  | UL2468, 22 AWG | 1,500 mm ±30 |

DC PLUG TYPE PART NUMBER KEY


**Plug Polarity:**  
P = Center Positive  
  
N = Center Negative  


**Plug Code:**  
X = Choose a code from the options below

**Plug Angle:**  
"blank" = Straight  
R = Right Angle

| Plug Polarity |             | Code            |                      | Dimensions (mm)  |      |     | Plug Angle |       |
|---------------|-------------|-----------------|----------------------|------------------|------|-----|------------|-------|
| Center Pos.   | Center Neg. | Option          | Type                 | A                | B    | C   | Straight   | Right |
| N/A           | N/A         | P1 <sup>1</sup> | Audio                | 3.5              | N/A  | 14  | •          | N/A   |
| •             | •           | 5               | Standard             | 5.5              | 2.1  | 9.5 | •          | •     |
| •             | •           | 6               | Standard             | 5.5              | 2.5  | 9.5 | •          | •     |
| •             | •           | 7               | Standard             | 3.5              | 1.35 | 9.5 | •          | •     |
| •             | •           | 8               | Standard             | 3.8              | 1.35 | 9.5 | •          | •     |
| •             | •           | 9               | Standard             | 3.8              | 1.05 | 9.5 | •          | •     |
| •             | •           | 10              | Locking <sup>2</sup> | 5.5              | 2.1  | 9.5 | •          | N/A   |
| •             | •           | 11              | Locking <sup>2</sup> | 5.5              | 2.5  | 9.5 | •          | N/A   |
| •             | •           | 12              | EIAJ-1               | 2.35             | 0.7  | 9.5 | •          | •     |
| •             | •           | 13              | EIAJ-2               | 4.0              | 1.7  | 9.5 | •          | •     |
| •             | •           | 14              | EIAJ-3               | 4.75             | 1.7  | 9.5 | •          | •     |
| N/A           | N/A         | ST              | Stripped and Tinned  |                  |      |     | N/A        | N/A   |
| N/A           | N/A         | MUB             | USB                  | Micro USB Type B |      |     | •          | N/A   |
| N/A           | N/A         | CUB             | USB                  | USB Type C       |      |     | •          | N/A   |

Note: 1. Tip positive  
2. Maximum insertion depth is 10mm  
3. Contact CUI for additional plug options



## REVISION HISTORY

| rev. | description                        | date       |
|------|------------------------------------|------------|
| 1.0  | initial release                    | 08/07/2015 |
| 1.01 | added models                       | 08/12/2015 |
| 1.02 | updated drawing                    | 11/10/2015 |
| 1.03 | added micro USB Type B plug option | 06/30/2016 |
| 1.04 | added audio plug option            | 11/07/2016 |
| 1.05 | added 62368-1 standard             | 08/31/2018 |
| 1.06 | company logo updated               | 09/21/2020 |
| 1.07 | updated dc plug options            | 11/19/2020 |
| 1.08 | safety marks updated               | 04/22/2021 |
| 1.09 | plug polarity symbols updated      | 09/16/2021 |
| 1.10 | dc plugs updated                   | 04/24/2022 |
| 1.11 | datasheet updated                  | 12/07/2024 |
| 1.12 | dc cord updated                    | 03/24/2025 |
| 1.13 | safeties updated                   | 05/21/2025 |

The revision history provided is for informational purposes only and is believed to be accurate.

**CUI INC**

a bel group

15575 SW Sequoia Pkwy #100  
Portland, OR 97224  
800.275.4899

Fax 503.612.2383  
**Belfuse.com**  
Tech.Support@psbel.com

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference, and
- (2) this device must accept any interference received, including interference that may cause undesired operation.

CUI offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.