


**SURFACE MOUNT
ULTRA FAST RECTIFIER**
REVERSE VOLTAGE – 50 to 1000 Volts
FORWARD CURRENT – 1.0 Amperes

FEATURES

- Glass passivated chip
- Ultra fast switching for high efficiency
- Low forward voltage drop and high current capability
- Low reverse leakage current

MECHANICAL DATA

- Case : Molded plastic
- Case Material: "Green" Molding compound, UL flammability classification 94V-0, (No Br. Sb. Cl.) "Halogen-free"
- Polarity : Indicated by cathode band
- Weight: 0.002 ounces , 0.069 grams (Approximate)

SMA


SMA		
DIM	MIN	MAX
A	4.06	4.57
B	2.29	2.92
C	1.27	1.63
D	0.15	0.31
E	4.83	5.59
F	0.05	0.20
G	2.01	2.40
H	0.76	1.52
All Dimensions in millimeter		

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

ABSOLUTE RATINGS

PARAMETER	SYMBOL	US1A	US1B	US1D	US1G	US1J	US1K	US1M	UNIT
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average rectified forward current	@ $T_L=110^\circ\text{C}$ I_F	1.0							A
Peak forward surge single half sine-wave	@ $t_p=8.3\text{ms}$ I_{FSM}	30							A
Operating and Storage temperature range	T_J, T_{STG}	-55 ~ +150							°C

STATIC ELECTRICAL CHARACTERISTICS

PARAMETER	TEST CONDITION	SYMBOL	MAX			UNIT
Forward voltage (Note 1)	$I_F=1\text{A}$ $T_J=25^\circ\text{C}$	V_F	1.0	1.3	1.7	V
Reverse leakage current at Rated DC blocking voltage	$T_J=25^\circ\text{C}$ $T_J=100^\circ\text{C}$	I_R	5.0	50		uA
Typical junction capacitance(Note 2)		C_j	20		10	pF

THERMAL CHARACTERISTICS

PARAMETER	SYMBOL	TYP	UNIT
Typical thermal resistance(Note 3)	R_{thJA} R_{thJL} R_{thJC}	60 22 18	°C/W

DYNAMIC ELECTRICAL CHARACTERISTICS

PARAMETER	SYMBOL	MAX	UNIT
Reverse recovery time	$I_F=0.5\text{A}, I_{rr}=0.25\text{A}, I_R=1.0\text{A}$ T_{rr}	50	75 nS

Note :

- (1) 300us pulse with, 2% duty cycle
- (2) Measured at 1.0MHz and reverse voltage of 4.0V DC.
- (3) Thermal resistance junction to Ambient, Lead and Case

REV. 10, Jun-2015, KSFA01

RATING AND CHARACTERISTIC CURVES
US1A thru US1M



FIG.1- FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL JUNCTION CAPACITANCE





FIG.5- TYPICAL REVERSE CHARACTERISTICS



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.