


390-057 Submersible EMI/RFI Cable Sealing Backshell with Strain Relief Type E - Direct Coupling - Low Profile




CONNECTOR DESIGNATORS A-B*-C-D-E-F G-H-J-K-L-S

* Conn. Desig. B See Note 5
DIRECT COUPLING



TYPE E INDIVIDUAL AND/OR OVERALL SHIELD TERMINATION




STYLE 2
(STRAIGHT
See Note 1)




* Length
 $\pm .060$ (1.52)
Minimum Order
Length 1.5 Inch
(See Note 4)




STYLE H
Heavy Duty
(Table X)



STYLE A
Medium Duty
(Table XI)



STYLE M
Medium Duty
(Table XI)



STYLE D
Medium Duty
(Table XI)

390-057
Submersible EMI/RFI Cable Sealing Backshell
with Strain Relief
Type E - Direct Coupling - Low Profile



See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: FRONT ADAPTER				
Shell Size	J Max - Conn. Designator			
	A-E-F			
	J-H-L-S	D-B-G-K	C	
08/09	1.180 (30.0)	1.440 (36.6)		
10/11	1.180 (30.0)	1.440 (36.6)		
12/13	1.180 (30.0)	1.440 (36.6)	1.735 (44.1)	
14/15	1.180 (30.0)	1.440 (36.6)	1.915 (48.6)	
16/17	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
18/19	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
20/21	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
22/23	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
24/25	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
28/29	1.610 (40.9)	1.560 (39.6)	1.915 (48.6)	
32/33	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)	
36	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)	
40	1.610 (40.9)	2.190 (55.6)	1.915 (48.6)	

TABLE IV: ELBOW DIMENSIONS						
Elbow Size	E Max	F Max	G Max	H Max		
03	.630 (16.0)	2.117 (53.8)	.636 (16.2)	2.067	(52.5)	
04	.630 (16.0)	2.117 (35.8)	.636 (16.2)	2.067	(52.5)	
06	.630 (16.0)	2.117 (35.8)	.710 (18.0)	2.187	(55.5)	
08	.692 (17.6)	2.179 (55.3)	.731 (18.6)	2.207	(39.1)	
10	.755 (19.2)	2.862 (72.7)	.825 (21.0)	2.867	(39.6)	
12	.848 (21.5)	2.972 (75.5)	.988 (25.1)	2.957	(41.4)	
16	1.036 (26.3)	3.159 (80.2)	1.087 (27.6)	3.132	(48.0)	
20	1.130 (28.7)	3.368 (85.5)	1.325 (33.7)	3.303	(50.8)	
24	1.255 (31.9)	3.408 (86.6)	1.337 (34.0)	3.453	(50.8)	
28	1.317 (33.5)	3.553 (90.2)	1.827 (46.4)	3.703	(55.1)	
32	1.348 (34.2)	3.646 (92.6)	2.027 (51.5)	3.753	(61.5)	

TABLE X: CABLE ENTRY						
Dash No.	T Max	V Max	Cable Range			
			Min	Max		
04	.780 (19.8)	.957 (24.3)	.125 (3.2)	.312	(7.9)	
06	.780 (19.8)	1.145 (29.1)	.250 (6.4)	.437	(11.1)	
08	.780 (19.8)	1.332 (33.8)	.387 (9.8)	.562	(14.3)	
10	.780 (19.8)	1.332 (33.8)	.350 (8.9)	.625	(15.9)	
12	.811 (20.6)	1.551 (39.4)	.500 (12.7)	.750	(19.1)	
16	.905 (23.0)	1.770 (45.0)	.625 (15.9)	.937	(23.8)	
20	1.092 (27.7)	2.113 (53.7)	.875 (22.2)	1.250	(31.8)	
24	1.124 (28.5)	2.363 (60.0)	1.000 (25.4)	1.375	(34.9)	
28	1.399 (35.5)	2.770 (70.4)	1.250 (31.8)	1.625	(41.3)	
32	1.399 (35.5)	3.020 (76.7)	1.437 (36.5)	1.875	(47.6)	

1. Metric dimensions (mm) are indicated in parentheses.
2. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
3. Designate Symbol T for 3 ring termination of individual and overall braid. Designate D for standard 2 ring termination of individual or overall braid.
4. Consult factory for shorter lengths on straight backshells.
5. When using Connector Designator B refer to pages 18 and 19 for part number development.

TABLE XI: CABLE ENTRY								
Dash No.	W Max	X Max	Y Max	Z Max	Cable Range			
					Min **	Max		
03*	.437 (11.1)	.760 (19.3)	.843 (21.4)	.630 (16.0)	.156 (4.0)	.250	(6.4)	
04*	.437 (11.1)	.760 (19.3)	.906 (23.0)	.755 (19.2)	.188 (4.8)	.312	(7.9)	
06*	.500 (12.7)	.760 (19.3)	1.093 (27.8)	.942 (23.9)	.281 (7.1)	.438	(11.1)	
08	.563 (14.3)	.760 (19.3)	1.187 (30.1)	1.067 (27.1)	.387 (9.8)	.562	(14.3)	
10	.563 (14.3)	.760 (19.3)	1.281 (32.5)	1.192 (30.3)	.375 (9.5)	.625	(15.9)	
12	.563 (14.3)	.760 (19.3)	1.500 (38.1)	1.380 (35.1)	.438 (11.1)	.750	(19.1)	
16	.656 (16.7)	1.073 (27.3)	1.719 (43.7)	1.535 (39.0)	.625 (15.9)	.938	(23.8)	
20	.656 (16.7)	1.323 (33.6)	2.062 (52.4)	1.848 (46.9)	.875 (22.2)	1.250	(31.8)	
24	.656 (16.7)	1.323 (33.6)	2.312 (58.7)	2.255 (57.3)	1.000 (25.4)	1.375	(34.9)	
28	1.188 (30.2)	1.572 (39.9)	2.719 (69.1)	2.505 (63.6)	1.250 (31.8)	1.625	(41.3)	
32*	1.187 (30.1)	1.572 (39.9)	2.969 (75.4)	2.755 (70.0)	1.437 (36.5)	1.875	(47.6)	
40*	1.125 (28.6)	1.572 (39.9)	3.531 (89.7)	3.255 (82.7)	1.875 (47.6)	2.375	(60.3)	

* Not available in Style M clamp.

** Not Applicable Style D