

P-Channel Power MOSFET

-20V, -6.5A, 26mΩ

FEATURES



- Fast switching
- Suitable for -1.8V Gate Drive Applications
- Pb-free plating
- RoHS Compliant
- Halogen-free

APPLICATIONS

- Battery Pack
- Portable Devices
- High-side loadswitch

KEY PERFORMANCE PARAMETERS

PARAMETER		VALUE	UNIT
V_{DS}		-20	V
$R_{DS(on)}$ (max)	$V_{GS} = -4.5V$	26	mΩ
	$V_{GS} = -2.5V$	32	
	$V_{GS} = -1.8V$	40	
Q_g		17	nC


SOT-26

Note: MSL 1 (Moisture Sensitivity Level) per J-STD-020

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		SYMBOL	LIMIT	UNIT
Drain-Source Voltage		V_{DS}	-20	V
Gate-Source Voltage		V_{GS}	± 10	V
Continuous Drain Current	$T_A = 25^\circ\text{C}$	I_D	-6.5	A
	$T_A = 100^\circ\text{C}$		-4.1	
Pulsed Drain Current (Note 1)		I_{DM}	-26	A
Total Power Dissipation @ $T_A = 25^\circ\text{C}$		P_D	1.6	W
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55 to +150	$^\circ\text{C}$

THERMAL PERFORMANCE

PARAMETER	SYMBOL	LIMIT	UNIT
Junction to Ambient Thermal Resistance (Note 2)	$R_{\theta JA}$	80	$^\circ\text{C/W}$

Notes:

1. Pulse Width $\leq 100\mu\text{s}$.
2. Device on a PCB FR4 with 1 in² (single layer, 2 oz thickness) copper area for drain connection.

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)						
PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Static						
Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = -250μA	BV _{DSS}	-20	--	--	V
Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = -250μA	V _{GS(TH)}	-0.3	-0.6	-1.0	V
Gate-Source Leakage Current	V _{GS} = ± 10V, V _{DS} = 0V	I _{GSS}	--	--	±100	nA
Drain-Source Leakage Current	V _{DS} = -20V, V _{GS} = 0V	I _{DSS}	--	--	-1	μA
	V _{DS} = -16V, T _J = 125°C		--	--	-10	
Drain-Source On-State Resistance (Note 3)	V _{GS} = -4.5V, I _D = -5A	R _{DS(on)}	--	19	26	mΩ
	V _{GS} = -2.5V, I _D = -4A		--	24	32	
	V _{GS} = -1.8V, I _D = -3A		--	32	40	
Forward Transconductance (Note 3)	V _{DS} = -10V, I _D = -5A	g _{fs}	--	16	--	S
Dynamic (Note 4)						
Total Gate Charge	V _{DS} = -10V, I _D = -5A, V _{GS} = -4.5V	Q _g	--	17	--	nC
Gate-Source Charge		Q _{gs}	--	2.2	--	
Gate-Drain Charge		Q _{gd}	--	3.7	--	
Input Capacitance	V _{DS} = -15V, V _{GS} = 0V, f = 1.0MHz	C _{iss}	--	1661	--	pF
Output Capacitance		C _{oss}	--	217	--	
Reverse Transfer Capacitance		C _{rss}	--	138	--	
Switching (Note 5)						
Turn-On Delay Time	V _{DD} = -10V, R _G = 25Ω, I _D = -1A, V _{GS} = -4.5V	t _{d(on)}	--	9.4	--	ns
Turn-On Rise Time		t _r	--	16	--	
Turn-Off Delay Time		t _{d(off)}	--	102	--	
Turn-Off Fall Time		t _f	--	49	--	
Source-Drain Diode						
Forward Voltage (Note 3)	I _S = -1A, V _{GS} = 0V	V _{SD}	--	--	-1	V

Notes:

- Pulse test: Pulse Width $\leq 300\mu s$, duty cycle $\leq 2\%$.
- Defined by design. Not subject to production test.
- Switching time is essentially independent of operating temperature.


ORDERING INFORMATION

ORDERING CODE	PACKAGE	PACKING
TSM260P02CX6 RFG	SOT-26	3000pcs / 7" Reel


CHARACTERISTICS CURVES (P-Channel)

($T_A = 25^\circ\text{C}$ unless otherwise noted)


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Gate-Source Voltage vs. Gate Charge



On-Resistance vs. Junction Temperature








On-Resistance vs. Gate-Source Voltage





CHARACTERISTICS CURVES (P-Channel)

($T_A = 25^\circ\text{C}$ unless otherwise noted)




CHARACTERISTICS CURVES (P-Channel)

($T_A = 25^\circ\text{C}$ unless otherwise noted)






Normalized gate threshold voltage vs Temperature



PACKAGE OUTLINE DIMENSIONS (Unit: Millimeters)

SOT-26



Y = Year Code
M = Month Code for Halogen Free Product
O = Jan **P** = Feb **Q** = Mar **R** = Apr
S = May **T** = Jun **U** = Jul **V** = Aug
W = Sep **X** = Oct **Y** = Nov **Z** = Dec
L = Lot Code

NOTES: UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. PACKAGE OUTLINE REFERENCE: JEDEC MO-178, VARIATION AB.
4. MOLDED PLASTIC BODY DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
5. DWG NO. REF: HQ2SD07-SOT26-027 REV A.

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.