HellermannTyton

Technical data sheet

Article number:
309-31903 TF24-19.1/9.5



Product Group	Heat shrinkable tubing 2:1 - flexible and transparent
Product Family	TF24
Material	Polyolefin, cross-linked (PO-X)
Colour	Transparent (CL)

Behaviour at Heat Shock	not dripping, not fluid, not cracking
Behaviour At Low Temperature	not cracking
Dielectric Strength	30 kV/mm
Elongation at break (min.)	450 %
Elongation At Heat Aging	250 %
Heat Aging Test	168h/175°C
Heat Shock Test	4h/250°C
Longitudinal Change After Shrinkage	+/-5% max.
Min. Shrink Temperature - °C	+110 °C
Operating Temperature	-55 °C to +135 °C
Package Content	50 m
Package Content packed in	reel
Recov. Ø d max.	9.5 mm
Shrink Ratio	2:1
Specifications	VG 95343-5:2016-10
Supplied Ø D min.	19.1 mm
Tensile Strength	20 MPa
Wall (WT)	0.76 mm
Water Absorption	0.2 %

HF RoHS

created on 5. June 2026, 4:01 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.