

Table 1. Electrical Performance

Parameter	Symbol	Min.	Typ	Max	Units
Nominal Frequency	F_{NOM}	12.000		60.000	MHz
Mode		Fundamental			
Operating Temperature Range	T_{OP}	0/70, -10/70, -20/70, -40/85			°C
Stability Over T_{OP} ¹	F_{STAB}	±10		±100	ppm
Frequency Tolerance ²	F_{TOL}		±10	±20	ppm
Load Capacitance	C_L	6		32	pF
Shunt Capacitance	C_o			5	pF
Drive Level			10	100	uW
Aging / 1st year (at 25 °C)	F_{AGE}			±5	ppm
Insulation Resistance		500			MOhm
Storage Temperature	T_{STO}	-40		90	°C
Equivalent Series Resistance					
Crystal Frequency	ESR				Ohm
12.001MHz-16.000MHz				80	
16.001MHz-20.000MHz				60	
20.001MHz-24.000MHz				50	
24.001MHz-60.000MHz				40	


Notes:

1. Referenced to the Frequency at 25 °C.
2. Frequency measured at 25 °C ± 3 °C.

Product is compliant to RoHS directive and fully compatible with lead free assembly.



Package Drawing and Pad LayOut



All Dimensions in mm

Part Marking:

MX = VXM4 Product Family

Y = Year

M = Month

A = January

B = February

C = March

D = April

E = May

F = June

G = July

H = August

I = September

J = October

K = November

L = December

C = Manufacturing Location


XXMXXX = frequency

Table 2. Environmental Compliance

Parameter	Conditions
Mechanical Shock	MIL-STD-883, Method 2002, Condition B
Mechanical Vibration	MIL-STD-883, Method 2007, Condition A
Temperature Cycle	MIL-STD-883, Method 1010, Condition B
Solderability	MIL-STD-202-210, Condition B
Gross and Fine Leak	MIL-STD-883, Method 1014
Altitude	MIL-STD-883, Method 1001, Condition B
Moisture Sensitivity Level	MSL 1
Contact Pads	Gold (0.3 μ m min) over Nickel
Weight	22 mg

Reliability & IR Compliance

Solderprofile:

**Table 3: Reflow Profile**

Parameter	Symbol	Value
PreHeat Time T_s -min T_s -max	t_s	60 sec Min, 260 sec Max 150°C 200°C
Ramp Up	R_{UP}	3 °C/sec Max
Time Above 217 °C	t_L	60 sec Min, 150 sec Max
Time To Peak Temperature	T_{AMB-P}	480 sec Max
Time at 260 °C	t_p	30 sec Max
Ramp Down	R_{DN}	6 °C/sec Max


Pads are Au over Ni and compatible with either SnPb or Pb free attachment.

MSL: 1

Tape & Reel

Table 4. Tape and Reel Dimensions (mm)

Tape												Reel							
A	B	C	D	E	F	G	H	J	K	L	M	A	B	C	D	E	W	T	
4.40	2.9	12.0	5.5	1.75	8.0	4.0	2.0	0.5	1.55	0.25	0.8	180	60	21.0	13.0	2.0	9.0	2.0	



Ordering Information

VXM4 - XXX - XX- xxMxxxxxxxxXX

Product

4.0 x 2.5mm, Crystal

Mode

1: Fundamental

Temp Stability

C: ± 10 ppm
D: ± 15 ppm
E: ± 20 ppm
F: ± 25 ppm
G: ± 30 ppm
H: ± 35 ppm
I: ± 40 ppm
J: ± 45 ppm
K: ± 50 ppm
S: ± 100 ppm

**Note: not all combination of options are available.
Other specifications may be available upon request.*

Packaging

TR: Tape and Reel
blank: Cut Tape / non Tape and Reel quantities
_SNPB: Tin lead solder dipped

Frequency in MHz

Load Capacitance

0: Series Resonance
06-32pF

Operating Temperature

E: -40 to 85 °C
J: -20 to 70 °C
W: -10 to 70 °C
T: 0 to 70 °C

Example:

VXM4-1EE-12-25M0000000TR

VXM4-1EE-12-25M0000000

VXM4-1EE-12-25M0000000_SNPB

Tape and Reel

Cut Tape

Tin lead solder dipped

Revision History

Revision Date	Approved	Description
August 29, 2016	RC	Initial datasheet for factory approval and release to customer.
August 10, 2018	FB	Update logo and contact information, add "SNPBDIP" ordering option
June 07, 2019	FB	Update logo and contact information, add Table 2 Environmental compliance, change "SNPBDIP" to "SNPB"
April 30, 2020	FB	Add tape and reel ordering option

Previous Ordering Information for Reference Only
Do Not Use to Build a New Part Number

VXM4-1A2-10M000

Package

Frequency

Mode

1 : Fundamental

Stability

A: ± 100 ppm over -20°C to 70°C
 B: ± 50 ppm over -20°C to 70°C
 C: ± 100 ppm over -40°C to 85°C
 D: ± 50 ppm over -40°C to 85°C
 E: ± 25 ppm over -20°C to 70°C
 F: ± 30 ppm over -20°C to 70°C

Load Capacitance

0: Series Resonator
 1: 16 pf
 2: 20 pf
 3: 32 pf
 4: 18 pf
 5: 10 pF
 6: 30 pf

The ordering codes for the VXM4 were changed in 2016. If you had ordered a specific code based off this ordering method, it is still available for purchase under the old code however no new part numbers will be created using this system.

Due to the change in the 8th character from numeric to alphabetic, there is no opportunity for overlap between the two ordering methods.

Contact Information

USA:

100 Watts Street
 Mt Holly Springs, PA 17065
 Tel: 1.717.486.3411
 Fax: 1.717.486.5920

Europe:

Landstrasse
 74924 Neckarbischofsheim
 Germany
 Tel: +49 (0) 7268.801.0
 Fax: +49 (0) 7268.801.281



Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATION OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING, BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly, or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip and Vectron names and logos are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.