





CUSTOMER DRAWING

REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1	CDXXXX	FIRST DRAWING	Nov.16,2017	YH
2	CDXXXX	CORRECT DRAFT ERROR	Jan.08,2018	YH
3	CDXXXX	ADD CORE OUT	Aug.31,2018	YH
4	CDXXXX	ADD CORE OUT	Dec.03,2018	YH



PN SYSTEM
SE10XXX2611111X

1	0.76UM Au
2	0.38UM Au
3	GOLD FLASH
4	0.76UM PdNi-GF

PIN COUNT
220
240
260
280

- NOTE:
- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC BLACK UL94-V0
CONTACT: COPPER ALLOY
BOARDLOCK: COPPER ALLOY
PICK UP CAP: SUS
 - PLATING:
CONTACT: MATING AREA: SEE PLATING SPEC OVER 127-254 UM NICKEL UNDERPLATED
SOLDER AREA: 127UM MIN TIN OVER 127-254 UM NICKEL UNDERPLATED
BOARDLOCK: 127UM MIN TIN OVER 127-254UM NICKEL UNDERPLATED
 - ELECTRICAL PERFORMANCE:
RATED CURRENT FOR SIGNAL PIN: 0.5A/PIN
 - MATERIAL SHOULD BE FULFILLED AMPHENOL SPEC # SSN002
 - ORDERING PN: REFER TO THE PN SYSTEM



UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	MATT
.X	+/-		Dec.03,2018
.XX	+/-	CHECKED	
.XXX	+/-	APPROVED	
FRACTIONS	+/-		
ANGLES	+/-		
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		INTERNAL DRAWING: CEC SE10XXX2611111X	
DIMENSIONS		ANGLE OF PROJECTION	
U.S.	INCHES		
(METRIC)	(mm)		

Amphenol



TITLE
Slim Cool Edge Connector
0.65mm Pitch, Vertical

SIZE	DRAWING NO.	REV.
A3C	SE10XXX2611111X	4
SCALE	NONE	SHEET 1 OF 2

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.


CUSTOMER DRAWING

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
		SEE SHEET 1		



RECOMMEND LAYOUT FOR MATING CARD
GENERAL TOLERANCE ±0.05

N	A	B	C	D	E
220	22.075	77.850	79.450	21.875	41.22
240	28.575	84.350	85.950	28.375	44.47
260	35.075	90.850	92.450	34.875	47.72
280	41.575	97.350	98.950	41.375	50.97



RECOMMEND LAYOUT FOR SOLDER PCB
GENERAL TOLERANCE ±0.05



UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC .X +/- 0.25 .XX +/- 0.20 .XXX +/- 0.15 FRACTIONS +/- ANGLES +/- 5° FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES DIMENSIONS U.S. INCHES (METRIC) (mm)		APPROVAL		DATE	Amphenol TITLE Slim Cool Edge Connector 0.65mm Pitch, Vertical SIZE DRAWING NO. A3C SE10XXX2611111X REV. 4	
		DRAWN	MATT	Dec.03,2018		
		CHECKED				
		APPROVED				
		DRAWING FILE :		INTERNAL\DRAWING\CE\C SE10XXX2611111X	SCALE	
		ANGLE OF PROJECTION			NONE	
					SHEET 2 OF 2	