OptiMOS™ Power-MOSFET

Features


- Optimized SyncFET for high performance Buck converter
- Integrated monolithic Schottky like diode
- Low profile (<0.7 mm)
- 100% avalanche tested
- 100% R_G Tested
- Double-sided cooling
- Compatible with DirectFET® package MX footprint and outline [1)]
- Qualified according to JEDEC[2)] for target applications
- Pb-free lead plating; RoHS compliant

Product Summary

V_{DS}	25	V
$R_{DS(on),max}$	1.3	mΩ
I_D	163	A
Q_{oss}	39	nC
Q_g(0V..10V)	62	nC

CanPAK™ M
MG-WDSON-2





Type	Package	Outline	Marking
BSB013NE2LXI	MG-WDSON-2	MX	02E2

Maximum ratings, at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	V_{GS}=10 V, T_C=25 °C	163	A
		V_{GS}=10 V, T_C=100 °C	103	
		V_{GS}=10 V, T_A=25 °C, R_{thJA}=45 K/W[3)]	36	
Pulsed drain current[4)]	$I_{D,pulse}$	T_C=25 °C	400	
Avalanche current, single pulse[5)]	I_{AS}	T_C=25 °C	40	
Avalanche energy, single pulse	E_{AS}	I_D=40 A, R_{GS}=25 Ω	130	mJ
Gate source voltage	V_{GS}		±20	V

[1)] CanPAK™ uses DirectFET ® technology licensed from International Rectifier Corporation. DirectFET® is a registered trademark of International Rectifier Corporation.

[2)] J-STD20 and JESD22

[3)] Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm2 (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

[4)] See figure 3 for more detailed information

[5)] See figure 13 for more detailed information

Downloaded from Arrow.com.

Maximum ratings, at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Power dissipation	P_{tot}	T_C=25 °C	57	W
		T_A=25 °C, R_{thJA}=45 K/W	2.8	
Operating and storage temperature	T_j, T_{stg}		-40 … 150	°C
IEC climatic category; DIN IEC 68-1				

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal characteristics						
Thermal resistance, junction - case	R_{thJC}	bottom	-	1.0	-	K/W
		top	-	-	2.2	
Device on PCB	R_{thJA}	6 cm^2 cooling area[3)]	-	-	45	
Electrical characteristics, at T_j=25 °C, unless otherwise specified						
Static characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0 V, I_D=10 mA	25	-	-	V
Breakdown voltage temperature coeffi	$dV_{(BR)DSS}/dT_j$	I_D=10 mA, referenced to 25 °C	-	15	-	mV/K
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=250 µA	1.2	-	2	V
Zero gate voltage drain current	I_{DSS}	V_{DS}=20 V, V_{GS}=0 V, T_j=25 °C	-	25	500	µA
		V_{DS}=20 V, V_{GS}=0 V, T_j=125 °C	-	4	-	mA
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	-	10	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=4.5 V, I_D=30 A	-	1.4	1.8	mΩ
		V_{GS}=10 V, I_D=30 A	-	1.1	1.3	
Gate resistance	R_G		0.3	0.6	1.2	Ω
Transconductance	g_{fs}	$\|V_{DS}\|>2\|I_D\|R_{DS(on)max}$, I_D=30 A	85	170	-	S

Downloaded from Arrow.com.


Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Dynamic characteristics						
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=12 V, f=1 MHz	-	4400	5900	pF
Output capacitance	C_{oss}		-	1900	2500	
Reverse transfer capacitance	C_{rss}		-	190	-	
Turn-on delay time	$t_{d(on)}$	V_{DD}=12 V, V_{GS}=10 V, I_D=30 A, R_G=1.6 Ω	-	5.4	-	ns
Rise time	t_r		-	6.4	-	
Turn-off delay time	$t_{d(off)}$		-	32	-	
Fall time	t_f		-	4.8	-	
Gate Charge Characteristics[6]						
Gate to source charge	Q_{gs}	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 4.5 V	-	10.5	14.0	nC
Gate charge at threshold	$Q_{g(th)}$		-	7.1	9.4	
Gate to drain charge	Q_{gd}		-	7.3	10.9	
Switching charge	Q_{sw}		-	10.7	15.5	
Gate charge total	Q_g		-	30	40	
Gate plateau voltage	$V_{plateau}$		-	2.4	-	V
Gate charge total	Q_g	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 10 V	-	62	83	nC
Gate charge total, sync. FET	$Q_{g(sync)}$	V_{DS}=0.1 V, V_{GS}=0 to 4.5 V	-	26	35	
Output charge	Q_{oss}	V_{DD}=12 V, V_{GS}=0 V	-	39	52	
Reverse Diode						
Diode continuous forward current	I_S	T_C=25 °C	-	-	57	A
Diode pulse current	$I_{S,pulse}$		-	-	228	
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=12 A, T_j=25 °C	-	0.55	0.7	V
Reverse recovery charge	Q_{rr}	V_R=15 V, I_F=I_S, di_F/dt=400 A/µs	-	5	-	nC

[6] See figure 16 for gate charge parameter definition

Downloaded from Arrow.com.


1 Power dissipation

$P_{tot}=f(T_C)$



2 Drain current


$I_D=f(T_C)$; $V_{GS}\geq 10$ V



3 Safe operating area

$I_D=f(V_{DS})$; $T_C=25$ °C; $D=0$


parameter: t_p



4 Max. transient thermal impedance

$Z_{thJC}=f(t_p)$

parameter: $D=t_p/T$




Downloaded from Arrow.com.

5 Typ. output characteristics

$I_D=f(V_{DS})$; $T_j=25$ °C


parameter: V_{GS}



6 Typ. drain-source on resistance

$R_{DS(on)}=f(I_D)$; $T_j=25$ °C


parameter: V_{GS}



7 Typ. transfer characteristics


$I_D=f(V_{GS})$; $|V_{DS}|>2|I_D|R_{DS(on)max}$

parameter: T_j



8 Typ. forward transconductance


$g_{fs}=f(I_D)$; $T_j=25$ °C



Downloaded from Arrow.com.


9 Drain-source on-state resistance

$R_{DS(on)}=f(T_j)$; $I_D=30$ A; $V_{GS}=10$ V




10 Typ. gate threshold voltage

$V_{GS(th)}=f(T_j)$; $V_{GS}=V_{DS}$; $I_D=10$ mA



11 Typ. capacitances


$C=f(V_{DS})$; $V_{GS}=0$ V; $f=1$ MHz



12 Forward characteristics of reverse diode

$I_F=f(V_{SD})$

parameter: T_j




Downloaded from Arrow.com.

13 Avalanche characteristics

I_{AS}=f(t_{AV}); R_{GS}=25 Ω


parameter: $T_{j(start)}$



14 Typ. gate charge

V_{GS}=f(Q_{gate}); I_D=30 A pulsed


parameter: V_{DD}




15 Typ. Drain-source leakage current

I_{DSS}=f(V_{DS}); V_{GS}=0 V

parameter: T_j




16 Gate charge waveforms



Downloaded from Arrow.com.

Package Outline

MG–WDSON–2



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	6.25	6.35	0.246	0.250
B	4.80	5.05	0.189	0.199
C	3.85	3.95	0.152	0.156
D	0.35	0.45	0.014	0.018
E	0.68	0.72	0.027	0.028
F	0.68	0.72	0.027	0.028
G	1.38	1.42	0.054	0.056
H	0.80	0.84	0.031	0.033
J	0.38	0.42	0.015	0.017
K	1.25	1.45	0.049	0.057
L	2.65	2.85	0.104	0.112
M	0.60	0.70	0.024	0.028
R	0.00	0.10	0.000	0.004
P	0.08	0.17	0.003	0.007

DOCUMENT NO.
Z8B00134455

SCALE 0 5 5 7.5mm


EUROPEAN PROJECTION

ISSUE DATE
05-05-2009

REVISION
03

Downloaded from Arrow.com.


Package Outline **MG-WDSON-2**



Dimensions in mm

Downloaded from Arrow.com.


CanPAK MX: Boardpads & Apertures



Dimensions in mm

Recommended stencil thickness 150 µm

Marking Layout



Downloaded from Arrow.com.

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2010 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Downloaded from Arrow.com.