





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECN-26-381559	24DEC2025	AP	SKN

NOTE:

1. MATERIAL:
HOUSING: PBT WITH 20% GF UL 94 V-0, BLACK COLOR
CONTACTS: BRASS.
SHELL:STEEL.
SCREW:BRASS.
SCREW LOCK:BRASS.
SCREW TORQUE:5kgf-cm MAX.
2. FINISH:
CONTACTS: GOLD PLATED 0.375μm[15μ"] MIN OR GOLD FLASH OVER PALLADIUM NICKEL PLATE 0.375μm[15μ"] MIN ON CONTACT AREA. MATTE TIN ON SOLDER TAIL 2.54μm [100μ"],WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL. FRONT SHELL: 2.54μm [100μ"] MIN. NICKEL PLATE. REAR SHELL: 1.27μm [50μ"] MIN NICKEL UNDERPLATE 2.54μm [100μ"] MIN BRIGHT TIN PLATE SCREW LOCK: 1.27μm [50μ"] MIN. NICKEL PLATED. BOARDLOCK: 1.27μm [50μ"] MIN NICKEL UNDERPLATE 1.27μm [50μ"] MIN MATTE TIN PLATE
3. WAVE SOLDER CAPABLE TO 265°C PER TE TEST SPEC. 109-202, CONDITION B.



RECOMMENDED PCB LAYOUT

9w D plg W B/L & 4-40 inserts	2301826-1
DESCRIPTION	TE PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	06FEB2017		 TE Connectivity Ltd.								
		CHK	06FEB2017										
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	06FEB2017		NAME						
mm				—									
		0 PLC ± —		PRODUCT SPEC									
		1 PLC ± 0.25		108—130013									
		2 PLC ± 0.15		APPLICATION SPEC									
		3 PLC ± —		—		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
		4 PLC ± —		—		A2		00779	C=2301826	—			
MATERIAL		FINISH		WEIGHT		0							
—		—		CUSTOMER DRAWING				SCALE	3:1	SHEET	1 of 4	REV	D1

D

C

B

A




D

C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT

2301826






				9w D plug W B/L & 4-40 s/lock		2301826-2						
				DESCRIPTION		TE PART NO						
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	06FEB2017		TE Connectivity Ltd.					
				CHK	06FEB2017							
				AJITH PAI								
				DAN GORENC								
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	06FEB2017		NAME					
mm				—								
		0 PLC ± —		PRODUCT SPEC								
		1 PLC ± 0.25		108-130013								
		2 PLC ± 0.15		APPLICATION SPEC								
		3 PLC ± —		—								
4 PLC ± —		ANGLES ± 2°		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A2 00779		C=2301826		—		
—		—		0								
CUSTOMER DRAWING				SCALE		3:1		SHEET		2 of 4	REV	D1

9w D plg W B/L & 4-40 s/lock	2301826-2
DESCRIPTION	TE PART NO

D-SUB VERTICAL
9P PLUG CONNECTOR

RESTRICTED TO	-
---------------	---


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



DETAIL A

P-DBS13-D43300


P-DBS13-U43300



SEE DETAIL A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI CHK DAN GORENC		06FEB2017 06FEB2017		 TE Connectivity Ltd.							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD — 06FEB2017		NAME D-SUB VERTICAL 9P PLUG CONNECTOR —							
		0 PLC ± — 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC 108-130013 APPLICATION SPEC —									
		MATERIAL —		WEIGHT 0						SIZE A2	CAGE CODE 00779	DRAWING NO C=2301826	RESTRICTED TO —
		FINISH —		CUSTOMER DRAWING						SCALE 3:1	SHEET 3 of 4	REV D1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



15.989	13.410	90	20	1800	2301826-2
13.325	10.746	90	20	1800	2301826-1
GROSS WEIGHT (Kg)	NET WEIGHT (Kg)	PCS/TRAY	TRAYS /CARTON	QUANTITY /PCS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI CHK DAN GORENC	06FEB2017 06FEB2017	 TE Connectivity Ltd.										
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME D-SUB VERTICAL 9P PLUG CONNECTOR -										
		APVD - PRODUCT SPEC 108-130013 APPLICATION SPEC -						SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT 0						A2		00779		C=2301826		-
		CUSTOMER DRAWING						SCALE		3:1		SHEET		4 of 4
		MATERIAL -		FINISH -										