






8	7	6	5	4	3	2	1
PART NUMBER	THICKNESS	MATERIAL	PLATING				
BMI-C-004-SN	0.10 ± 0.010 [0.0040]	BeCu ALLOY 25 TH01	MATTE TIN				



UNITS: MM [INCH]	<div>Laird</div>			LAIRD DRAWING NUMBER: BMI-C-004-SN-SALES	
TOLERANCES:  X.X = ± 0.4 X.XX = ± 0.2 X.XXX = ± 0.1				THIS IS AN UNCONTROLLED SALES DRAWING. THE DIMENSIONAL CHARACTERISTICS AND TOLERANCES OF THIS PART SHOWN ON THIS DRAWING AS A REFERENCE TO THE DIMENSIONAL SPECIFICATIONS OF THE LAIRD STANDARD PRODUCTION DRAWING FOR THIS PART. ANY SUBSEQUENT CHANGES TO THE STANDARD PART SPECIFICATION WILL SUPERSEDE THIS SALES DRAWING.	
3RD ANGLE PROJECTION					
ANGULAR: X° = ± 3° X.X° = ± 1.0°	DESIGNED IN SOLIDWORKS	SIZE B			
	SCALE: 10:1	SHEET 1 OF 1			