

Dimension

DIM A	Nx5,08
DIM B	(N-1)x5,08



N=Number of poles

POLES	TOL
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35
17p-24p	±0.40


Material

- Item 1 Terminal housing: Thermoplastic UL94V-0, Green
Item 2 Clamp: Brass ,Ni plated
Item 3 Wire guard solder pin: Brass ,Tin plated
Item 4 Terminal screw: Steel Zinc plating "slot type"

Electrical cULus/ FMKO
Voltage rating: 300VAC/300VAC
Current rating: 16A/17.5A
Wire range: 0.5-1.5mm²
Solid wire(AWG): 12-28
Stranded wire(AWG): 12-28
Torque: 3.5Lb-in./0.5N.m
Screw: M3
Wire strip length: 6-7mm
Withstanding Voltage: 1.6kV/2.5kV
Operating temperature: -40°C to +115°C
Soldering temperature: 250°C±10°C/5Sec
Safety Approval:  



N=Number of contacts



RoHS compliant



File No.: E349947

Scale	1:1						Customer-No.
TOLERANCE					Date	Name	
X.	±0.50			Drawn	10.12.2009	Dean	
X.X	±0.30			Approved	19.04.2016	Winnie	
X.XX	±0.10	③	Add the UL File No.				ASSMANN WSW-No. A-TB508-V1XXH
DIM	TOL	②	Modify drawing		19.04.2010	Dean	Drawing-No.
X.°	±1°	①	Drawn		10.12.2009	Dean	ASS 3927 CO
Angle	TOL		Modification		Date	Name	Replace

