




ENG. NO: A-70287-1000 / 1048			
DIM. C		6.10/[.240]	
DIM. E (REF.)		3.18/[.125]	
DIM. L (REF.)		11.56/[.455]	
MATING SIDE PLATING		TIN	
DIM. D (MEASURE PT.)		2.54/[.100]	
P.C. BOARD SIDE PLATING		TIN	
DIM. F (MEASURE PT.)		1.27/[.050]	
RETENTIVE PIN LOCATION		SEE NOTE 6, SHEET 1	
PACKAGING		BULK - PK-70873-0353	
CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER
04	70287-1000	54	70287-1025
06	70287-1001	56	70287-1026
08	70287-1002	58	70287-1027
10	70287-1003	60	70287-1028
12	70287-1004	62	70287-1029
14	70287-1005	64	70287-1030
16	70287-1006	66	70287-1031
18	70287-1007	68	70287-1032
20	70287-1008	70	70287-1033
22	70287-1009	72	70287-1034
24	70287-1010	74	70287-1035
26	70287-1011	76	70287-1036
28	70287-1012	78	70287-1037
30	70287-1013	80	70287-1038
32	70287-1014	82	70287-1039
34	70287-1015	84	70287-1040
36	70287-1016	86	70287-1041
38	70287-1017	88	70287-1042
40	70287-1018	90	70287-1043
42	70287-1019	92	70287-1044
44	70287-1020	94	70287-1045
46	70287-1021	96	70287-1046
48	70287-1022	98	70287-1047
50	70287-1023	100	70287-1048
52	70287-1024		

ENG. NO: A-70287-1098 / 1146			
DIM. C		6.10/[.240]	
DIM. E (REF.)		3.18/[.125]	
DIM. L (REF.)		11.56/[.455]	
MATING SIDE PLATING		15 GOLD	
DIM. D (MEASURE PT.)		2.54/[.100]	
P.C. BOARD SIDE PLATING		TIN	
DIM. F (MEASURE PT.)		1.27/[.050]	
RETENTIVE PIN LOCATION		SEE NOTE 6, SHEET 1	
PACKAGING		BULK - PK-70873-0353	
CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER
04	70287-1098	54	70287-1123
06	70287-1099	56	70287-1124
08	70287-1100	58	70287-1125
10	70287-1101	60	70287-1126
12	70287-1102	62	70287-1127
14	70287-1103	64	70287-1128
16	70287-1104	66	70287-1129
18	70287-1105	68	70287-1130
20	70287-1106	70	70287-1131
22	70287-1107	72	70287-1132
24	70287-1108	74	70287-1133
26	70287-1109	76	70287-1134
28	70287-1110	78	70287-1135
30	70287-1111	80	70287-1136
32	70287-1112	82	70287-1137
34	70287-1113	84	70287-1138
36	70287-1114	86	70287-1139
38	70287-1115	88	70287-1140
40	70287-1116	90	70287-1141
42	70287-1117	92	70287-1142
44	70287-1118	94	70287-1143
46	70287-1119	96	70287-1144
48	70287-1120	98	70287-1145
50	70287-1121	100	70287-1146
52	70287-1122		

ENG. NO: A-70287-1196 / 1244			
DIM. C		6.10/[.240]	
DIM. E (REF.)		3.18/[.125]	
DIM. L (REF.)		11.56/[.455]	
MATING SIDE PLATING		30 GOLD	
DIM. D (MEASURE PT.)		2.54/[.100]	
P.C. BOARD SIDE PLATING		TIN	
DIM. F (MEASURE PT.)		1.27/[.050]	
RETENTIVE PIN LOCATION		SEE NOTE 6, SHEET 1	
PACKAGING		BULK - PK-70873-0353	
CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER
04	70287-1196	54	70287-1221
06	70287-1197	56	70287-1222
08	70287-1198	58	70287-1223
10	70287-1199	60	70287-1224
12	70287-1200	62	70287-1225
14	70287-1201	64	70287-1226
16	70287-1202	66	70287-1227
18	70287-1203	68	70287-1228
20	70287-1204	70	70287-1229
22	70287-1205	72	70287-1230
24	70287-1206	74	70287-1231
26	70287-1207	76	70287-1232
28	70287-1208	78	70287-1233
30	70287-1209	80	70287-1234
32	70287-1210	82	70287-1235
34	70287-1211	84	70287-1236
36	70287-1212	86	70287-1237
38	70287-1213	88	70287-1238
40	70287-1214	90	70287-1239
42	70287-1215	92	70287-1240
44	70287-1216	94	70287-1241
46	70287-1217	96	70287-1242
48	70287-1218	98	70287-1243
50	70287-1219	100	70287-1244
52	70287-1220		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
DIMENSION UNITS		SCALE		CURRENT REV DESC: MIGRATED TO NX				molex						
MM/INCH		1:1												
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 614461				SALES ASSY-HIGH TEMP. DUAL ROW, .025" SQ PINS .100" GRID W/ RET. PINS						
4 PLACES		MM	INCH	DRWN: ABABU012019/03/13				PRODUCT CUSTOMER DRAWING						
3 PLACES		±	± 0.005	CHK'D: NMANE022019/03/26										
2 PLACES		± 0.13	± 0.01	APPR: MRAMAKRISHNA2019/03/26										
1 PLACE		± 0.25	±	INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION		
0 PLACES		±	±	DRWN: MKIPPER2009/11/02				SD-70287-004		PSD	001	A1		
ANGULAR TOL ± 0.5 °				APPR: FSMITH2009/11/02										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	SHEET NUMBER	
						C-SIZE		70287		SEE CHART		GENERAL MARKET		2 OF 3

ENG. NO: A-70287-1294			
DIM. C		6.10/[.240]	
DIM. E (REF.)		3.18/[.125]	
DIM. L (REF.)		11.56/[.455]	
MATING SIDE PLATING		TIN	
DIM. D (MEASURE PT.)		2.54/[.100]	
P.C. BOARD SIDE PLATING		TIN	
DIM. F (MEASURE PT.)		1.27/[.050]	
RETENTIVE PIN LOCATION		ROW B - CKTS 1, 5 (SEE NOTE 6, SHEET 1)	
PACKAGING		BULK - PK-70873-0353	
		VOID PIN LOCATION	
CKTS	MATERIAL NUMBER	ROW	LOCATION
10	70287-1294	A	2, 3
		B	2, 3

ENG. NO: A-70287-1295			
DIM. C		5.84/[.230]	
DIM. E (REF.)		2.97/[.117]	
DIM. L (REF.)		11.10/[.437]	
MATING SIDE PLATING		15 GOLD	
DIM. D (MEASURE PT.)		2.54/[.100]	
P.C. BOARD SIDE PLATING		TIN	
DIM. F (MEASURE PT.)		1.27/[.050]	
RETENTIVE PIN LOCATION		ROW B - CKTS 3, 4 (SEE NOTE 6, SHEET 1)	
PACKAGING		BULK - PK-70873-0353	
		VOID PIN LOCATION	
CKTS	MATERIAL NUMBER	ROW	LOCATION
10	70287-1295	A	1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

MM/INCH

SCALE

1:1

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

CURRENT REV DESC: MIGRATED TO NX

EC NO: 614461

DRWN: ABABU012019/03/13

CHK'D: NMANE022019/03/26


APPR: MRAMAKRISHNA2019/03/26

INITIAL REVISION:

DRWN: MKIPPER2009/11/02

APPR: FSMITH2009/11/02

THIRD ANGLE PROJECTION



DRAWING

C-SIZE

SERIES

70287

SALES ASSY-HIGH TEMP.

DUAL ROW, .025" SQ PINS .100" GRID W/ RET. PINS

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

SD-70287-004

DOC TYPE

PSD

DOC PART

001

REVISION

A1

MATERIAL NUMBER

SEE CHART

CUSTOMER

GENERAL MARKET

SHEET NUMBER

3 OF 3

DOCUMENT STATUS

P1

RELEASE DATE

2019/03/2612:56:10

11

10

9

8

7

6

5

4

3

2

1