

Representative Image

Catalog No. A18-10

Description: NONINS RING TERM, 22-16, NO10, META

UPC No 786210803029

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Sta-Kon Non-Insulated Ring Terminal AWG 22-19, stud size #10

Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indentor or double indentor (recommended for solid wire). Serrated barrel increases grip on wire.

Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

Classifications

Brand Name	Sta-Kon
Standard	UL E9809

Dimensions

Wire Size	22-16 AWG

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	22-16

by ABB

Downloaded from Arrow.com.

ETIM	EC001052 Solderless copper terminals for copper conductors
Material	Copper
Surface protection	Tinned
Stud size (imperial)	10

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.