






PC card drilling dimensions(after plating)

(thickness 1.60±0.20mm)



GENERAL CHARACTERISTICS : SEE DRAWING C01–8646–0000

LEAD FREE PART NUMBER

SHELL	A± 0.38	B± 0.12	C± 0.10	$D\pm_{0}^{0.25}$	E± 0.07	$G\pm_{0}^{0.25}$	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	5.90	D09P33E4U*00LF	D09P33E6U*00LF
15	39.14	33.32	25.18	25.12	19.18	5.90	D15P33E4U*00LF	D15P33E6U*00LF
25	53.03	47.04	39.12	38.84	33.12	5.70	D25P33E4U*00LF	D25P33E6U*00LF
37	69.32	63.50	55.68	55.30	49.68	5.70	D37P33E4U*00LF	D37P33E6U*00LF
							200 Mating	500 Mating

X--> ØT = UNC 4–40
L--> ØT = M3

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101	projection	product family
–				tolerances unless otherwise specified				D–SUB
ltr	ecn no	dr	date	angles	linear	.0±.1	MM	title
D	ELX–I–21045	AB	2015/06/04	0°±2°		.00±0.1	scale 2:1	MALE DELTA–D RIGHT ANGLE WITH NUT & METAL PLATE
						.000±0.1		
				dr	JOHN SLEEBA	2003/12/27		dwg no C01–8646–0851 sheet 1 of 1 size A3
				engr	ALIAS BABU	2015/06/04		
				chr	MITHUN PAUL	2015/06/04		
				appd	BIJU K PAUL	2015/06/04		type Product Customer Drawing
sheet index	revision sheet	D 1						

form: A3

FCIconnect.com
Copyright FCI
Downloaded from Arrow.com.

PDS: Rev :D STATUS:Released Printed: Jun 05, 2015