


LTR	REVISION	DATE	APPD
F	120722-GZ01: UPDATED LED AND LENS FOR P/N: RPLH16-03-02-02	12-08-22	HF

ITEMS 1 - 4

ITEM 5

ITEM 6




NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].

BILL OF MATERIALS

ITEM	DESCRIPTION	QTY
1	LAMPHOLDER (RYNITE FR530 [UL94V0]) WITH (2) 12K, 2 WATT METAL FILM RES.	1
2	WASHER Ø1.0X.188 (NEOPRENE) OPTIONAL	1
3	WASHER Ø1.0X.063 (NEOPRENE) OPTIONAL	2
4	NUT (ALUMINUM 6061T6)	1
5	LED LAMP (28V - BIPOLAR POLARITY)	1
6	LENS (POLYCARBONATE [UL94V2])	1



RPLH16-03-XX-02X

HOLDER SIZE INCOMING VOLTAGE LENS COLOR LED BULB STYLE



ELECTRICAL / OPTICAL CHARACTERISTICS (Ta = 25°C)

RPLH16-03-01-02	250Vdc	0.010 A	—	635	RED	RPLH16-03	RPLB-0201-28V	RPLL16-CRF
RPLH16-03-02-02	250Vdc	0.010 A	—	610	YELLOW	RPLH16-03	RPLB-0204-28V	RPLL16-CYF
RPLH16-03-03-02A	250Vdc	0.010 A	—	595	YELLOW/AMBER	RPLH16-03	RPLB-0204-28V	RPLL16-CAF
RPLH16-03-04-02	250Vdc	0.010 A	—	519	GREEN	RPLH16-03	RPLB-0206-28V	RPLL16-CGF
RPLH16-03-05-02	250Vdc	0.010 A	—	462	BLUE	RPLH16-03	RPLB-0208-28V	RPLL16-CBF
RPLH16-03-06-02	250Vdc	0.010 A	—	8000K	WHITE	RPLH16-03	RPLB-0209-28V	RPLL16-TWF
RPLH16-03-07-02	250Vdc	0.010 A	—	8000K	CLEAR	RPLH16-03	RPLB-0210-28V	RPLL16-CWF
LEDTRONICS PART NO.	INPUT VOLTAGE, V	CURRENT (A)	POWER (W)	λ P nm COLOR TEMP. (K)	COLOR EMITTED	LAMP HOLDER PART NO.	LED LAMP PART NO.	LENS PART NO.

LED[®]
LEDTRONICS,™ INC.
23105 KASHIWA COURT
TORRANCE, CA 90505

-PROPRIETARY-
This document contains Proprietary information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.

.XXX ± .010 TOLERANCE PER ANSI-Y14.5
.XX ± .025 (UNLESS OTHERWISE STATED)
ANGLES ± 0°.30'
FRACT. ± 1/32

TITLE

RPLH16-03-0X-02X

DWG NO

H1602004

SCALE

1:1

SHEET

1 OF 1

DATE

09-14-98

CODE
IDENT NO.
8Z410

DWG BY
SMA
09-14-98

CHK BY

QA
LUV
12-08-22

MFG
LD
12-13-22

R&D
LUV
12-08-22