

STS32XXXXUXXX

TVS Diode ESD suppressor



Product features

- 2000 Watts peak pulse power per line
 $t_p = 8/20 \mu s$
- Solid-state silicon-avalanche technology
- Protects one uni-directional I/O line
- Low clamping voltage
- Low leakage current
- High surge capability
- Meets moisture sensitivity level (MSL) 3
- Molding compound flammability rating:
UL 94V-0
- Termination finish: Tin

Applications

- Cellular handsets and accessories
- Microprocessor based equipment
- Potable electronics
- Notebooks, desktops, and servers
- Portable instrumentation
- Power lines
- Peripherals

Environmental compliance and general specifications

- IEC61000-4-2 (ESD)
 - Up to ± 30 kV (air)
 - Up to ± 30 kV (contact)
- IEC61000-4-5 (Lightning) Up to 110 A (8/20 μs)



Ordering part number

	ST	S32	1	050	U	852
Family	_____	_____	_____	_____	_____	_____
Package (S32- SOD-323)	_____	_____	_____	_____	_____	_____
Number of channels (1)	_____	_____	_____	_____	_____	_____
Operating voltage (050- 5 V)	_____	_____	_____	_____	_____	_____
Bi/Uni directional (U- Uni)	_____	_____	_____	_____	_____	_____
Capacitance (852- 850 pF)	_____	_____	_____	_____	_____	_____

Pin out/functional diagram



SOD-323



Pin Configuration



Powering Business Worldwide

Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit
STS32XXXXULXXX			
Peak pulse power dissipation on 8/20 μ s waveform	P_{pp}	2000	W
ESD per IEC 61000-4-2 (Air)	V_{ESD}	+/-30	kV
ESD per IEC 61000-4-2 (Contact)		+/-30	
Lead soldering temperature	T_L	+260 (10 seconds)	°C
Operating junction temperature range	T_J	-55 to +125	°C
Storage temperature range	T_{STG}	-55 to +150	°C

Electrical characteristics

(+25 °C)

STS321050U852

Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	-	-	-	5	V_{RWM} (V)
Reverse breakdown voltage	$I_t = 1$ mA	6	7	8	V_{BR} (V)
Reverse leakage current	$V_{RWM} = 5$ V	-	-	1	I_R (μ A)
Clamping voltage	$I_{pp} = 50$ A, $t_p = 8/20$ μ s	-	11	13	V_c (V)
	$I_{pp} = 110$ A, $t_p = 8/20$ μ s	-	14	17	V_c (V)
Junction capacitance	$V_{RWM} = 0$ V, $f = 1$ MHz	-	850	1050	C_J (pF)

STS321070U722

Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	-	-	-	7	V_{RWM} (V)
Reverse breakdown voltage	$I_t = 1$ mA	7.5	8	9	V_{BR} (V)
Reverse leakage current	$V_{RWM} = 7$ V	-	-	1	I_R (μ A)
Clamping voltage	$I_{pp} = 50$ A, $t_p = 8/20$ μ s	-	12	15	V_c (V)
	$I_{pp} = 100$ A, $t_p = 8/20$ μ s	-	15	18	V_c (V)
Junction capacitance	$V_{RWM} = 0$ V, $f = 1$ MHz	-	720	900	C_J (pF)

Electrical characteristics
(+25 °C)


STS321120U372

Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	-	-	-	12	V_{RWM} (V)
Reverse breakdown voltage	$I_t = 1$ mA	13	14.4	17	V_{BR} (V)
Reverse leakage current	$V_{RWM} = 12$ V	-	-	1	I_R (μA)
Clamping voltage	$I_{PP} = 20$ A, $t_p = 8/20$ μs	-	16	19	V_c (V)
	$I_{PP} = 40$ A, $t_p = 8/20$ μs	-	20	24	V_c (V)
	$I_{PP} = 70$ A, $t_p = 8/20$ μs	-	22	28	V_c (V)
	$t_p = 8/20$ μs	-	-	-	-
Junction capacitance	$V_{RWM} = 0$ V, $f = 1$ MHz	-	370	450	C_J (pF)

STS321150U332





Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	-	-	-	15	V_{RWM} (V)
Reverse breakdown voltage	$I_t = 1$ mA	16	17.2	20	V_{BR} (V)
Reverse leakage current	$V_{RWM} = 15$ V	-	-	1	I_R (μA)
Peak pulse current	$t_p = 8/20$ μs	-	-	55	I_{PP} (A)
Clamping voltage	$I_{PP} = 25$ A, $t_p = 8/20$ μs	-	22	25	V_c (V)
	$I_{PP} = 50$ A, $t_p = 8/20$ μs	-	26	28	V_c (V)
	$I_{PP} = 55$ A, $t_p = 8/20$ μs	-	27	30	V_c (V)
	$t_p = 8/20$ μs	-	-	-	-
Junction capacitance	$V_{RWM} = 0$ V, $f = 1$ MHz	-	330	400	C_J (pF)

Mechanical parameters, pad layout- mm/inches




Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
A	1.60	1.80	0.063	0.071
B	0.25	0.35	0.010	0.014
C	2.50	2.75	0.098	0.108
D	0.00	1.00	0.000	0.039
E	1.20	1.40	0.047	0.055
F	0.08	0.15	0.003	0.006
L	0.475 REF		0.019 REF	
L1	0.25	0.40	0.010	0.016
H	0.00	0.10	0.000	0.004
P	3.00	3.00	0.118	0.118
P1	0.80	0.80	0.031	0.031

Part marking



Packaging information mm/inches


Drawing not to scale.
Supplied in tape and reel packaging, 3,000 parts per 7" diameter reel (EIA-481 compliant)




Symbol	Millimeters	Inches
A	1.46±0.05	0.057±0.002
B	2.90±0.05	0.114±0.002
C	1.25±0.05	0.049±0.002
d	±1.50±0.1	±0.059±0.004
E	1.75±0.1	0.069±0.004
F	3.50±0.1	0.138±0.004
P0	4.0±0.1	0.157±0.004
P	4.0±0.1	0.157±0.004
P1	2.0±0.1	0.079±0.004
W	8.00+0.3/-0.1	0.315+0.012/-0.004
D	±178.0±2	±7.008±0.079
D1	54.40±1	2.142±0.039
D2	13.0±1	0.512±0.039
G	R78.0±1	R3.071±0.039
H	R25.60±1	R1.008±0.039
I	R6.50±1	R0.256±0.039
W1	9.50±1	0.374±0.039
W2	12.30±1	0.484±0.039

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)


V- I curve characteristics (Uni-directional)




Pulse waveform (8/20 μ s)



Pulse derating curve



ESD waveform



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-120 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	30 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11145 BU-MC20127
September 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

