

COAXIAL CONNECTOR, SHV, 50 Ohm, Straight bulkhead cable jack
(female)
24_SHV-50-3-1/133_N

Properties

- Suitable for all high voltage applications up to 5 kV DC or 3.5 kV rms
- Used in nuclear instruments or test and measurement equipment
- Voltages are valid for both, the mated and the unmated condition.



Product configuration		
Gender	Standard	
jack	IEC 60498_MIL-STD-348A/314	
Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Copper, Tin plated	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating
Electrical data		
Impedance	50 Ω	
Interface frequency	0.3 GHz	
Mechanical data		
Weight	0.0242 kg	
Mating cycles	500	
Cable entry centre contact	crimped	
Cable entry outer contact	crimped	
Environmental data		
Operation temperature	-65 °C ... 165 °C	

COAXIAL CONNECTOR, SHV, 50 Ohm, Straight bulkhead cable jack (female)

24_SHV-50-3-1/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22641281	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22641281	24_SHV-50-3-1/133_NE	Single

Suitable cables	
Cable group	U7 - 3 mm / 50 Ohm
Suitable cables	RG_58_C/U
	G_03232

Additional Information	
Remarks	High voltage connector Working voltage (at sea level) 3.5 kV rms, 50Hz (depending on cable)
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544757	76_Z-0-3-51	Crimping dies
22543185	76_Z-0-3-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2582 / Date of publication: 11.07.2025 / uncontrolled copy