

Part Number : [311000042](#)
Product Description : H-DAC 64 2.54mm4 Way
Right-Angle Header Assembly, Polarization C
Series Number : 31100
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[311000042_sd.pdf](#)
[PK-31300-707-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[AS-31067-100-001.pdf](#)
[PS-31100-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Boric acid per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	31100
Description	H-DAC 64 2.54mm4 Way Right-Angle Header Assembly, Polarization C
Application	Automotive, Wire-to-Board
Comments	Polarization Option C, Brown
Component Type	PCB Header
Product Name	H-DAC 64
UPC	822350654975

Electrical

Current - Maximum per Contact	5.0A, 7.0A
Voltage - Maximum	500V DC

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Brown
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No

Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Modified Polystyrene
Net Weight	1.776/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	3.52mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Sealed	Unsealed
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +100°C
Termination Interface Style	Through Hole
Terminal Size	0.635

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.54mm H-DAC 64, 4 Way Receptacle Assembly, Single Row, Polarization C	<u>310681012</u>

This document was generated on Aug 08, 2026