

6

5

4

3



2

1



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/20/11	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max.

Current rating: 1 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5,000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant

Positions: 8, 10, 20, 26, 30, 34, 40, 44, 50, 60, 68, 80, 100

A = .050 [1.27] x No. of Spaces

B = .050 [1.27] x No. of Spaces + .366 [9.29]

C = .050 [1.27] x No. of Spaces + .311 [7.89]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES
X .XX ± .10
X .XX ± .020
X .XX ± .015
X .XX ± .010

APPROVALS
DATE

DRAWN AY 9/20/11

CHECKED

APPROVED

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE .050" x .100" BOX HEADER, STRAIGHT

GOLD PLATED, PCB TYPE, HI-TEMP

SIZE PART NO. HBHR-A1-XX-VG-HT

X

REF: S00041T SCALE: NTS SHEET 1 OF 1

6

5

4

3

2

1