





## Low Profile Miniature Glass Passivated Single-Phase Surface Mount Bridge Rectifiers



Case Style DFS Low Profile

### LINKS TO ADDITIONAL RESOURCES



3D Models

| PRIMARY CHARACTERISTICS |                                                 |
|-------------------------|-------------------------------------------------|
| $I_{F(AV)}$             | 1.5 A                                           |
| $V_{RRM}$               | 50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V |
| $I_{FSM}$               | 50 A                                            |
| $I_R$                   | 5 $\mu$ A                                       |
| $V_F$ at $I_F = 1.5$ A  | 1.1 V                                           |
| $T_J$ max.              | 150 °C                                          |
| Package                 | DFS low profile                                 |
| Circuit configuration   | Quad                                            |

### FEATURES

- Low profile: typical height of 2.5 mm
- UL recognition, file number E54214
- Ideal for automated placement
- High surge current capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

RoHS  
COMPLIANT

### TYPICAL APPLICATIONS

General purpose use in AC/DC bridge full wave rectification for SMPS, lighting ballaster, adapter, battery charger, home appliances, office equipment, and telecommunication applications.

### MECHANICAL DATA

**Case:** DFS low profile

Molding compound meets UL 94 V-0 flammability rating  
Base P/N-E3 - RoHS-compliant, commercial grade

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD22-B102

E3 suffix meets JESD 201 class 1A whisker test

**Polarity:** as marked on body

| MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)                     |                 |             |           |           |           |           |           |           |                  |
|-----------------------------------------------------------------------------|-----------------|-------------|-----------|-----------|-----------|-----------|-----------|-----------|------------------|
| PARAMETER                                                                   | SYMBOL          | DFL 15005S  | DFL 1501S | DFL 1502S | DFL 1504S | DFL 1506S | DFL 1508S | DFL 1510S | UNIT             |
| Maximum repetitive peak reverse voltage                                     | $V_{RRM}$       | 50          | 100       | 200       | 400       | 600       | 800       | 1000      | V                |
| Maximum RMS voltage                                                         | $V_{RMS}$       | 35          | 70        | 140       | 280       | 420       | 560       | 700       | V                |
| Maximum DC blocking voltage                                                 | $V_{DC}$        | 50          | 100       | 200       | 400       | 600       | 800       | 1000      | V                |
| Maximum average forward output rectified current at $T_A = 40$ °C           | $I_{F(AV)}$ (1) | 1.5         |           |           |           |           |           |           | A                |
| Peak forward surge current single half sine-wave superimposed on rated load | $I_{FSM}$       | 50          |           |           |           |           |           |           | A                |
| Rating for fusing ( $t < 8.3$ ms)                                           | $I^2t$          | 10          |           |           |           |           |           |           | A <sup>2</sup> s |
| Operating junction and storage temperature range                            | $T_J, T_{STG}$  | -55 to +150 |           |           |           |           |           |           | °C               |

#### Note

(1) Units mounted on PCB with 0.51" x 0.51" (13 mm x 13 mm) copper pads

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PARAMETER                                                         | TEST CONDITIONS         | SYMBOL                        | DFL 15005S | DFL 1501S | DFL 1502S | DFL 1504S | DFL 1506S | DFL 1508S | DFL 1510S | UNIT |
|-------------------------------------------------------------------|-------------------------|-------------------------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|------|
| Max. instantaneous forward voltage drop per diode                 | 1.5 A                   | V <sub>F</sub>                | 1.1        |           |           |           |           |           |           | V    |
| Maximum DC reverse current at rated DC blocking voltage per diode | T <sub>A</sub> = 25 °C  | I <sub>R</sub>                | 5.0        |           |           |           |           |           |           | μA   |
|                                                                   | T <sub>A</sub> = 125 °C |                               | 500        |           |           |           |           |           |           |      |
| Typical junction capacitance per diode                            |                         | C <sub>J</sub> <sup>(1)</sup> | 16         |           |           |           |           |           |           | pF   |

**Note**

(1) Measured at 1.0 MHz and applied reverse voltage of 4.0 V

**THERMAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PARAMETER                  | SYMBOL                | DFL 15005S | DFL 1501S | DFL 1502S | DFL 1504S | DFL 1506S | DFL 1508S | DFL 1510S | UNIT |
|----------------------------|-----------------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|------|
| Typical thermal resistance | $R_{\theta JA}^{(1)}$ | 40         |           |           |           |           |           |           | °C/W |
|                            | $R_{\theta JL}^{(1)}$ | 15         |           |           |           |           |           |           |      |

**Note**

(1) Units mounted on PCB with 0.51" x 0.51" (13 mm x 13 mm) copper pads

**ORDERING INFORMATION** (Example)

| PREFERRED P/N  | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                    |
|----------------|-----------------|------------------------|---------------|----------------------------------|
| DFL1506S-E3/45 | 0.341           | 45                     | 50            | Tube                             |
| DFL1506S-E3/77 | 0.341           | 77                     | 1500          | 13" diameter paper tape and reel |



**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)




Fig. 1 - Forward Current Derating Curve Per Diode




Fig. 4 - Typical Reverse Characteristics Per Diode




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Diode




Fig. 5 - Typical Junction Capacitance Per Diode





Fig. 3 - Typical Forward Voltage Characteristics Per Diode



**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.