SIEMENS

Data sheet 3LD2250-0TK13



SENTRON, switch disconnector 3LD, EMERGENCY-OFF switch, 3- pole, Iu: 32 A, operational power / at AC-23 A at 400 V: 11.5 kW, front-mounted, knob-operated mechanism, red/yellow, central fixing 22.5 mm of the handle

Model	
product brand name	SENTRON
product designation	Switch disconnector
design of the product	EMERGENCY-STOP switch
display version for switch position indicator manual operation	1 ON - 0 OFF
type of switch	front mounted
design of the actuating element	selector switch
color of the actuating element	red
design of handle	knob-operated mechanism, red/yellow
type of the driving mechanism motor drive	No
General technical data	
number of poles	3
size of switch disconnector	2
mechanical service life (operating cycles) typical	100 000
electrical endurance (operating cycles)	
● at AC-23 A at 690 V	6 000
operating frequency maximum	50 1/h
degree of pollution	3
Voltage	
insulation voltage rated value	690 V
surge voltage resistance rated value	6 kV
operating voltage	
● at AC rated value	690 V
operating frequency rated value	
● minimum	50 Hz
● maximum	60 Hz
Protection class	
protection class IP	IP65
degree of protection NEMA rating	1, 3R, 4X, 12
protection class IP on the front	IP65
Dissipation	
power loss [W] for rated value of the current at AC in hot operating state per pole	1.8 W
Main circuit	
operational current	
● at AC-21 at 690 V rated value	32 A
● at AC-21 A at 240 V rated value	32 A
● at AC-21 A at 400 V rated value	32 A

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

● at AC-21 A at 440 V rated value	32 A
● at AC-23 A at 400 V rated value	22 A
operating power	
● at AC-23 A at 240 V rated value	6 kW
● at AC-23 A at 400 V rated value	12 kW
● at AC-23 A at 440 V rated value	11.5 kW
● at AC-23 A at 690 V rated value	12 kW
● at AC-3 at 240 V rated value	5.5 kW
● at AC-3 at 400 V rated value	10 kW
● at AC-3 at 690 V rated value	9.5 kW
Auxiliary circuit	
number of CO contacts for auxiliary contacts	0
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
operating voltage of auxiliary contacts at AC maximum	500 V
continuous current of the auxiliary contact rated value	10 A
insulation voltage of the auxiliary switch rated value	500 V
Suitability	
suitability for use main switch	Yes
suitability for use switch disconnector	Yes
suitability for use EMERGENCY OFF switch	Yes
suitability for use safety switch	Yes
suitability for use maintenance/repair switch	Yes
Product details	
product feature can be locked into OFF position	Yes
Accessories	
product extension optional	
● motor drive	No
● voltage trigger	No
number of connectable NC contacts for auxiliary contacts attachable maximum	2
number of connectable NO contacts for auxiliary contacts attachable maximum	2
number of connectable CO contacts for auxiliary contacts attachable maximum	0
number of bracket locks maximum	2
hasp thickness of the bracket locks	4 ... 6 mm
Short circuit	
conditional short-circuit current with line-side fuse protection	
● at 690 V by gG fuse rated value	50 kA
let-through current with closed switch	
● at 240 V for combination switch + gG fuse maximum	4.5 kA
● at 440 V for combination switch + gG fuse maximum	4.5 kA
● at 690 V for combination switch + gG fuse maximum permissible	5 kA
I2t value with closed switch	
● at 240 V for combination switch + gG fuse maximum	9 kA²·s
● at 440 V for combination switch + gG fuse maximum	9 kA²·s
● at 690 V for combination switch + gG fuse maximum	9 kA²·s
design of the fuse link	
● for short-circuit protection of the main circuit required	fuse gL/gG: 40 A
● for short-circuit protection of the auxiliary switch required	fuse gL/gG: 10 A
operational current of upstream fuse rated value	40 A
according UL	
operational current at AC according to UL 508/UL 60947-4-1 rated value	32 A
operating voltage at AC at 50/60 Hz according to UL 508/UL 60947-4-1 rated value	600 V
active power [hp] at AC at 480 V according to UL 508/UL 60947-4-1 rated value	20

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

active power [hp] at AC at 600 V according to UL 508/UL 60947-4-1 rated value	20
short-time withstand current (SCCR) at 600 V according to UL 508/UL 60947-4-1	5 kA
continuous current of upstream fuse according to UL rated value	80 A
type of fuse according to UL	RK5
Connections	
AWG number as coded connectable conductor cross section solid maximum	
•	8
•	14
type of connectable conductor cross-sections for copper conductor	
• solid	1x (1,5...16mm²)
• finely stranded with core end processing	1x (1,5...10mm²)
• stranded	1x (1,5...16mm²)
type of connectable conductor cross-sections for auxiliary contacts	
• solid	2x (0.75 ... 2.5 mm²), 1x 4 mm²
• finely stranded with core end processing	2x (0.75 ... 1.5 mm²), 1x 2.5 mm²
• stranded	2x (0.75 ... 2.5 mm²), 1x 4 mm²
type of electrical connection	
• for main current circuit	box terminal
• for auxiliary contacts	connection terminals
Mechanical Design	
height	71 mm
width	49 mm
depth	109.5 mm
type of device	fixed mounting
fastening method	Built-in unit fixed-mounted version
fastening method	
• 4-hole front mounting	No
• front mounting with central attachment	Yes
• rail mounting	No
Net Weight	183 g
Environmental conditions	
ambient temperature during operation	
• minimum	-25 °C
• maximum	55 °C
ambient temperature during storage	
• minimum	-25 °C
• maximum	55 °C

Approvals Certificates

Environment		**General Product Approval**			
Environmental Con-firmations	Environmental Con-firmations	CCC	cULus	VDE	Miscellaneous

General Product Approval		**Maritime application**		
EAC	Confirmation	CE EG-Konf.	DNV	Lloyd's Register LRS	PRS

other


Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.


Confirmation





Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD2250-0TK13
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3LD2250-0TK13
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD2250-0TK13
CAx-Online-Generator
https://www.siemens.com/cax
Tender specifications
https://www.siemens.com/specifications
Characteristic curves
https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod__no>











Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.





last modified: 10/14/2025

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.