



Part Number : [2130830005](#)

Product Description : Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Top Mount, Single Row, Surface Mount, Gold (Au) Plating, Waterproof

Series Number : 213083

Status : Active

Product Category : I/O Connectors



Documents and Resources

Drawings

[2130830005 sd.pdf](#)

[2130830005-PK0.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications


[2130830005AS-000.pdf](#)

[2130830001-000.pdf](#)

[2130830005TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	213083
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Top Mount, Single Row, Surface Mount, Gold (Au) Plating, Waterproof
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Standard	USB 2.0
Type	C
UPC	193264522279

Electrical

Current - Maximum per Contact	5.0A
Grounding to Panel	None
Shielded	No
Shield Type	Full Shield

Voltage - Maximum	30V AC/DC
-------------------	-----------

Physical

Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	Nylon
Mounting Style	Top-Mount
Net Weight	0.501/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.80mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IPx8

Mates With / Use With

Mates with Part(s)

Description	Part Number
USB Shielded I/O Type C Plugs	<u>105444</u>

This document was generated on Apr 15, 2026