
MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

BRIDGE PRESSURE SENSOR

CATALOG LISTING
136PC15A2

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH




GENERAL OPERATING CHARACTERISTICS

PRESSURE RANGE	0 TO 775 mmHg (0 TO 15 PSIA)
OVERPRESSURE	2325 mmHg (45 PSIA)
TEMPERATURE RANGES	
STORAGE	-55°C TO +125°C
OPERATE	-40°C TO +85°C
COMPENSATED	0°C TO +50°C
SUPPLY VOLTAGE	16 VDC MAX
INPUT RESISTANCE	6800 OHM TYP

ELECTRICAL PERFORMANCE @ 25°C AND 10.00±.01 VDC SUPPLY

OUTPUT VOLTAGE	
NULL (0 PSIA)	.000 mV TYP
REFERENCE (2 PSIA)	-13.3±2 mV
FULL SCALE (15 PSIA)	-100.0 VDC TYP
SPAN (2 TO 15 PSIA)	-86.7±2.5 mV
SENSITIVITY	6.7 mV/PSI TYP
LINEARITY (B.F.S.L.)	.12% SPAN MAX
HYSTERESIS & REPEATABILITY	.17% SPAN TYP
TEMPERATURE ERROR (0°C TO +50°C)	
NULL SHIFT	4.0 mV MAX
SPAN SHIFT	3.46% SPAN MAX

CIRCUIT DIAGRAM



OUTPUT "A" INCREASES AS INPUT PRESSURE INCREASES
OUTPUT "B" DECREASES AS INPUT PRESSURE INCREASES

NOTES
1 - TERMINALS ARE PLATED FOR SOLDERING
2 - LIMIT SOLDERING TO 315°C MAX FOR 10 SECONDS MAX
3 - INPUT MEDIA DRY GASES ONLY; CONNECTION SIDE OF SENSOR

THIRD ANGLE PROJECTION

SCALE 2 : 1

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT

ANSI Y14.5M-1982 APPLIES

CATALOG LISTING 136PC15A2 PAGE 1 OF 1 ISSUE 3 M
RELEASE NO. CO-77378 REPLACES -

REVISIONS
A 207062 TSM 18DEC02
B 0000791 C S L 7 JUL 03

PTC/CAD 2D
DRAWN TSM 18DEC02 CHECK SAV 18DEC02 CHECK CHECK

Downloaded from Arrow.com.