

Multilayer Ceramic Chip Capacitors

Product Top Page

Search by Part No.

Search by Characteristics

Cross Reference

Catalog

Tech Notes

Technical Support Tools

FAQ

CGA3E3NP02E102J080AA



TDK item description ? CGA3E3NP02E102JT****

Applications



Automotive Grade

Feature

Mid

Mid Voltage (100 to 630V)

150°C

High Temperature Application

AEC-Q200

AEC-Q200


Series

CGA3(1608) [EIA 0603]

Status



Production



Images are for reference only and show exemplary products.

PDF file of this page



Buy Now



Contact



Documents

Catalog

Specification

RoHS Certificate

SVHC/REACH Certificate

Characterization Sheet

Promotion Video

Sample Kits

Size

Length(L) 1.60mm ±0.10mm

Width(W) 0.80mm ±0.10mm

Thickness(T) 0.80mm ±0.10mm

Terminal Width(B) 0.20mm Min.

Terminal Spacing(G)

Recommended Land Pattern (PA) 0.70mm to 1.00mm(Flow Soldering)
0.60mm to 0.80mm(Reflow Soldering)

Recommended Land Pattern (PB) 0.80mm to 1.00mm(Flow Soldering)
0.60mm to 0.80mm(Reflow Soldering)

Recommended Land Pattern (PC) 0.60mm to 0.80mm(Flow Soldering)
0.60mm to 0.80mm(Reflow Soldering)

Electrical Characteristics

Capacitance 1nF ±5%

Rated Voltage 250VDC

Temperature Characteristic ? NP0(0±30ppm/°C)

Q (Min.) 1000

Insulation Resistance (Min.) 10000MΩ

Other

Soldering Method Wave (Flow)
Reflow


AEC-Q200 Yes

Packing Punched (Paper)Taping [180mm Reel]


Package Quantity 4000pcs







Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)

Impedance



ESR





Products

» Search by Part No. » Search by Characteristics » Distributor Inventory Check

- | | |
|--|---|
| » Capacitors | » Anechoic Chambers and Radio Wave Absorbers |
| » Inductors (Coils) | » Power Supplies |
| » EMC Components | » Magnets |
| » RF Components and Modules | » Flash Storages |
| » Voltage / Current / Temperature Protection Devices | » Wireless Power Transfer |
| » Sensors and Sensor Systems | » FA Systems |
| » Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones | » Transparent Conductive Film |
| » Transformers | » Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB) |
| » Ferrites and Accessories | » Solar Cells |
| » Noise Suppressing / Magnetic Sheet | » Biosensor |

Application Guides

Technical Support

Tech Library

Environment

Contact

News

Home

- About TDK
- TDK Worldwide

