
G9EA-1

DC Power Relays (60-A, 100-A Models)

DC Power Relays Capable of Interrupting High-voltage, High-current Loads



- A compact relay (73 x 36 x 67.2 mm (L x W x H)) capable of switching 400-V 60-A DC loads. (Capable of interrupting 600 A at 300 VDC max.)
- The switching section and driving section are gas-injected and hermetically sealed, allowing these compact relays to interrupt high-capacity loads. The sealed construction also requires no arc space, saves space, and helps ensure safe applications.
- Downsizing and optimum design allow no restrictions on the mounting direction.
- Terminal Cover and DIN Track Adapters are also available for industrial applications.
- UL/CSA standard UL508 approved.

⚠ Refer to **"DC Power Relays Common Precautions"**.

■Model Number Legend

G9EA-□-□-□-□
1 2 3 4

1. Number of Poles
1: 1 pole

2. Contact Form
Blank: SPST-NO

3. Coil Terminals
B: M3.5 screw terminals
Blank: Lead wire output

4. Special Functions
CA: High-current conduction (100 A)

■List of Models

Classification	Terminals		Contact form	Rated coil voltage	Model
	Coil terminals	Contact terminals			
Switching/current conduction models	Screw terminals	Screw terminals	SPST-NO	12 VDC 24 VDC 48 VDC 60 VDC 100 VDC	**G9EA-1-B**
	Lead wires				**G9EA-1**
High-current conduction models	Screw terminals				**G9EA-1-B-CA**
	Lead wires				**G9EA-1-CA**

Note 1. Two M5 screws are provided for the contact terminal connection.
Note 2. Two M3.5 screws are provided for the coil terminal connection.

■Ratings

●Coil

Item Rated voltage	Rated current (mA)	Coil resistance (Ω)	Must-operate voltage (V)	Must-release voltage (V)	Maximum voltage (V)	Power consumption (W)
12 VDC	417	28.8	75% max. of rated voltage	8% min. of rated voltage	130% of rated voltage (at 23°C within 10 minutes)	Approx. 5 W
24 VDC	208	115.2				
48 VDC	102	469.3				
60 VDC	86.2	695.7				Approx. 5.2 W
100 VDC	53.6	1864				Approx. 5.4 W

Note 1. The figures for the rated current and coil resistance are for a coil temperature of 23°C and have a tolerance of ±10%.
Note 2. The figures for the operating characteristics are for a coil temperature of 23°C.
Note 3. The figure for the maximum voltage is the maximum voltage that can be applied to the relay coil.

●Contacts

Item	Resistive load	
	G9EA-1(-B)	G9EA-1(-B)-CA
Rated load	60 A at 400 VDC, 100 A at 120 VDC	30 A at 400 VDC
Rated carry current	60 A	100 A
Maximum switching voltage	400 V	400 V
Maximum switching current	100 A	30 A

Downloaded from Arrow.com.

■Characteristics


Item	Model	G9EA-1(-B)	G9EA-1(-B)-CA
Contact resistance 1		30 mΩ max. (0.6 mΩ typical)	10 mΩ max. (0.3 mΩ typical)
Contact voltage drop		0.1 V max. (for a carry current of 60 A)	0.1 V max. (for a carry current of 100 A)
Operate time		50 ms max.	
Release time		30 ms max.	
Insulation resistance	Between coil and contacts	1,000 MΩ min.	
	Between contacts of the same polarity	1,000 MΩ min.	
Dielectric strength *2	Between coil and contacts	2,500 VAC, 1 min	
	Between contacts of the same polarity	2,500 VAC, 1 min	
Impulse withstand voltage *3		4,500 V	
Vibration resistance	Destruction	10 to 55 to 10 Hz, 0.75-mm single amplitude (Acceleration: 2.94 to 88.9 m/s²)	
	Malfunction	10 to 55 to 10 Hz, 0.75-mm single amplitude (Acceleration: 2.94 to 88.9 m/s²)	
Shock resistance	Destruction	490 m/s²	
	Malfunction	196 m/s²	
Mechanical endurance *4		200,000 ops. min.	
Electrical endurance (resistive load) *5		120 VDC, 100 A, 3,000 ops. min.	400 VDC, 30 A, 1,000 ops. min.
		400 VDC, 60 A, 3,000 ops. min.	120 VDC, 30 A, 2,500 ops. min.
		400 VDC, 30 A, 30,000 ops. min.	–
Short-time carry current		100 A (10 min)	150 A (10 min)
Maximum interruption current		600 A at 300 VDC (5 times)	–
Overload interruption		180 A at 400 VDC (100 times min.)	100 A at 120 VDC (150 times min.)
Reverse polarity interruption		–60 A at 200 VDC (1,000 times min.)	–
Ambient operating temperature		–40 to 70°C (with no icing or condensation)	
Ambient operating humidity		5% to 85% RH	
Weight (including accessories)		Approx. 310 g	

Note. The above values are initial values at an ambient temperature of 23°C unless otherwise specified.
*1. The contact resistance was measured with 1A at 5VDC using the voltage drop method.
*2. The insulation resistance was measured with a 500-VDC megohmmeter.
*3. The impulse withstand voltage was measured with a JEC-212 (1981) standard impulse voltage waveform (1.2 × 50 μs).
*4. The mechanical endurance was measured at a switching frequency of 3,600 operations/hr.
*5. The electrical endurance was measured at a switching frequency of 60 operations/hr.


■Engineering Data

G9EA-1(-B) Switching/Current Conduction Models


● Maximum Switching Capacity




● Electrical Endurance (Switching Performance)



● Electrical Endurance (Interruption Performance)




● Carry Current vs Energizing Time




Downloaded from Arrow.com.

G9EA-1(-B)-CA High-current Conduction Models


● Maximum Switching Capacity



● Electrical Endurance (Switching Performance)




● Carry Current vs Energizing Time




All G9EA-1 Models


● Must-operate Voltage and Must-release Voltage Distributions




● Time Characteristic Distributions



● Vibration Malfunction




● Vibration Resistance




Characteristics were measured after applying vibration at a frequency of 10 to 55 Hz (single amplitude of 0.75 mm) to the test piece (not energized) for 2 hours each in 3 directions. The percentage rate of change is the average value for all of the samples

● Shock Malfunction



The value at which malfunction occurred was measured after applying shock to the test piece 3 times each in 6 directions along 3 axes.

● Shock Resistance





Characteristics were measured after applying a shock of 490 m/s^2 to the test piece 3 times each in 6 directions along 3 axes. The percentage rate of change is the average value for all of the samples.


Downloaded from Arrow.com.


■Dimensions (Unit: mm)

● Models with Screw Terminals
G9EA-1-B(-CA)











Dimension (mm)	Tolerance (mm)
10 or lower	±0.3
10 to 50	±0.5
50 or higher	±1

Terminal Arrangement/ Internal Connections
(TOP VIEW)





Note: Be sure to connect terminals with the correct polarity. Coils do not have polarity.


Mounting Hole Dimensions
(TOP VIEW)



● Models with Lead Wires
G9EA-1(-CA)









Dimension (mm)	Tolerance (mm)
10 or lower	±0.3
10 to 50	±0.5
50 or higher	±1

Terminal Arrangement/ Internal Connections
(TOP VIEW)



Note: Be sure to connect terminals with the correct polarity. Coils do not have polarity.


Mounting Hole Dimensions
(TOP VIEW)




Downloaded from Arrow.com.

■Options (Unit: mm)

● Terminal Cover
P9EA-C







* Dimensions of cutouts for wiring.

Note: Be sure to remove the cutouts for wiring that are located in the wiring outlet direction before installing the Terminal Cover.

Dimension (mm)	Tolerance (mm)
10 or lower	±0.3
10 to 50	±0.5
50 or higher	±1

● DIN Track Adapter
P9EA-D





Dimension (mm)	Tolerance (mm)
10 or lower	±0.3
10 to 50	±0.5
50 or higher	±1

Downloaded from Arrow.com.

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact

Americas
https://components.omron.com/us
Asia-Pacific
https://components.omron.com/ap
Korea
https://components.omron.com/kr
Europe
https://components.omron.com/eu
China
https://components.omron.com.cn
Japan
https://components.omron.com/jp

© OMRON Corporation 2007-2022 All Rights Reserved.
In the interest of product improvement, specifications are subject to change without notice.

Cat. No. J186-E1-02
1122 (0207)

Downloaded from Arrow.com.