






Order Code	TCK-130
Inductance	22 µH ±15% (at 100 kHz / 250 mV)
Impedance (DCR)	550 mΩ max.
Rated Current	0.58 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-130



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	3.0 ±0.5
B	3.5 ±0.5
C	2.0 ±0.5
D	1.2 typ.
E	3.6
F	1.7
G	0.8

All specifications valid at +25°C, unless otherwise stated.