

COAXIAL CONNECTOR, BNT, 50 Ohm, Straight bulkhead receptacle, jack (female)
22_BNT-50-0-2/103_N

Properties



Product configuration		
Interface type	Gender	Standard
BNT	jack	HUBER+SUHNER-BNT

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	3 GHz

Mechanical data	
Weight	0.0075 kg
Mating cycles	500
Chassis torque	2 Nm
Flange type	round flange / dia. 12.5
Tab style	solder end

Environmental data	
Operation temperature	-50 °C ... 125 °C

COAXIAL CONNECTOR, BNT, 50 Ohm, Straight bulkhead receptacle, jack (female)
22_BNT-50-0-2/103_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22541070	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22541070	22_BNT-50-0-2/103_NE		Single
Additional Information			
Remarks		Triaxial Connector Front mount chassis connector	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2812 / Date of publication: 12.07.2025 / uncontrolled copy