



+ CONNECTORS

CARD EDGE POWER CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
MULTI-BEAM CE 2X13 P + 2X24 S, RA
[MULTI-BEAM](#) | [MULTI-BEAM CE](#)

2212115-1
TE Internal Number: 2212115-1

- Contact Current Rating (Max) (A) 21
- Number of Power Positions 26
- Centerline (Pitch) 7.26 mm [.286 in]
- Number of Signal Positions 48
- Circuit Application Power, Signal

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**



DOCUMENTATION

Product Drawings

CONNECTOR ASSEMBLY, MULTI-BEAM CE, POWER/SIGNAL, RIGHT ANGLE, SOLDER MOUNT
PDF
English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

Multi-Beam CE Power Card Edge Connector

PDF

English

Application Specification

Application Spec For Multi-Beam Card Edge

PDF

English

Qualification Test Report

Multi-Beam CE Power Card Edge Connector

PDF

English

Agency Approvals

UL Report

SEC II POWER CONNECTOR SERIES REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Configuration Features

Number of Power Positions 26

Number of Signal Positions 48

Number of Dual Positions 13

Number of Positions 74

Number of Single Positions 0

Electrical Characteristics

Operating Voltage (VDC) 100

Operating Voltage 100

Contact Features

Contact Current Rating (Max) (A) 21

Contact Mating Area Plating Material Gold

Contact Mating Area Plating Thickness .76 µm [30 µin]

Termination Features

Termination Method to PC Board Through Hole - Solder

Housing Features

Centerline (Pitch) 7.26 mm [.286 in]

Dimensions

Power Contact Centerline 7.3 mm [.286 in]

Operation/Application

Circuit Application Power, Signal