


**CGPE - 105**  
Flexible, Commercial Grade, Polyolefin,  
Heat-Shrinkable Tubing



**Table 1: Dimensions** mm(inches)

| Size  | As Supplied                 |       | Recovered                   |       |                    |      |         |      |         |      |
|-------|-----------------------------|-------|-----------------------------|-------|--------------------|------|---------|------|---------|------|
|       | Inside Diameter Minimum (D) |       | Inside Diameter Maximum (d) |       | Wall Thickness (W) |      |         |      |         |      |
|       |                             |       |                             |       | Minimum            |      | Maximum |      | Nominal |      |
|       | mm                          | in.   | mm                          | in.   | mm                 | in.  | mm      | in.  | mm      | in.  |
| 3/64  | 1.17                        | .046  | 0.58                        | .023  | 0.33               | .013 | 0.48    | .019 | 0.40    | .016 |
| 1/16  | 1.60                        | .063  | 0.79                        | .031  | 0.35               | .014 | 0.50    | .020 | 0.43    | .017 |
| 3/32  | 2.36                        | .093  | 1.17                        | .046  | 0.43               | .017 | 0.58    | .023 | 0.50    | .020 |
| 1/8   | 3.17                        | .125  | 1.57                        | .062  | 0.43               | .017 | 0.58    | .023 | 0.50    | .020 |
| 3/16  | 4.74                        | .187  | 2.36                        | .093  | 0.43               | .017 | 0.58    | .023 | 0.50    | .020 |
| 1/4   | 6.35                        | .250  | 3.17                        | .125  | 0.56               | .022 | 0.71    | .028 | 0.64    | .025 |
| 3/8   | 9.50                        | .375  | 4.74                        | .187  | 0.56               | .022 | 0.71    | .028 | 0.64    | .025 |
| 1/2   | 12.70                       | .500  | 6.35                        | .250  | 0.56               | .022 | 0.71    | .028 | 0.64    | .025 |
| 3/4   | 19.05                       | .750  | 9.50                        | .375  | 0.69               | .027 | 0.84    | .033 | 0.76    | .030 |
| 1     | 25.40                       | 1.000 | 12.70                       | .500  | 0.76               | .030 | 1.01    | .040 | 0.88    | .035 |
| 1-1/2 | 38.10                       | 1.500 | 19.05                       | .750  | 0.86               | .034 | 1.17    | .046 | 1.01    | .040 |
| 2     | 50.80                       | 2.000 | 25.40                       | 1.000 | 0.96               | .038 | 1.32    | .052 | 1.14    | .045 |


For More Details See CGPE - 105 Specification, TEC - 108 - 120008

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2017 CGPE-105

|                                                                                     |  |                                |            |                                                                                                                                                               |                    |
|-------------------------------------------------------------------------------------|--|--------------------------------|------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| DIMENSIONS:<br>mm                                                                   |  | DWN<br>J. Bitter               | 07-JUNE-17 | <br>TE Connectivity<br>305 Constitution Drive<br>Menlo Park, CA 94025 USA |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                              |  | CHK<br>—                       | —          |                                                                                                                                                               |                    |
| 0 PLC ± —<br>1 PLC ± —<br>2 PLC ± —<br>3 PLC ± —<br>4 PLC ± —<br>ANGLES ± —         |  | APVD<br>—                      | —          |                                                                                                                                                               |                    |
|                                                                                     |  | PRODUCT SPEC<br>TEC-108-120008 |            | NAME<br>CGPE - 105<br>Flexible, Commercial Grade,<br>Polyolefin, Heat - Shrinkable Tubing                                                                     |                    |
|                                                                                     |  | APPLICATION SPEC<br>—          |            | SIZE<br>A4                                                                                                                                                    | CAGE CODE<br>06090 |
|                                                                                     |  | WEIGHT<br>0                    |            | DRAWING NO<br>CGPE-105                                                                                                                                        |                    |
|  |  | CUSTOMER DRAWING               |            | SCALE<br>None                                                                                                                                                 | SHEET<br>1 OF 1    |
|                                                                                     |  |                                |            | REV<br>E1                                                                                                                                                     |                    |