

2SC4883/4883A

Silicon NPN Epitaxial Planar Transistor (Complement to type 2SA1859/A)

Application : Audio Output Driver and TV Velocity-modulation

Absolute maximum ratings (Ta=25°C)

Symbol	Ratings		Unit
	2SC4883	2SC4883A	
V _{CB0}	150	180	V
V _{CE0}	150	180	V
V _{EB0}	6		V
I _c	2		A
I _B	1		A
P _c	20(Tc=25°C)		W
T _j	150		°C
T _{stg}	-55 to +150		°C


Electrical Characteristics (Ta=25°C)

Symbol	Conditions	Ratings		Unit
		2SC4883	2SC4883A	
I _{CB0}	V _{CB} =	150	180	μA
I _{EB0}	V _{EB} =6V	10max		μA
V _{(BR)CEO}	I _c =10mA	150min	180min	V
h _{FE}	V _{CE} =10V, I _c =0.7A	60 to 240		
V _{CE(sat)}	I _c =0.7A, I _B =70mA	1.0max		V
f _r	V _{CE} =12V, I _E =-0.7A	120typ		MHz
COB	V _{CB} =10V, f=1MHz	30typ		pF


Typical Switching Characteristics (Common Emitter)

V _{CC} (V)	R _L (Ω)	I _c (A)	V _{BB1} (V)	V _{BB2} (V)	I _{B1} (mA)	I _{B2} (mA)	t _{on} (μs)	t _{stg} (μs)	t _f (μs)
20	20	1	10	-5	100	-100	0.5typ	1.5typ	0.5typ


External Dimensions FM20(TO220F)




I_c-V_{CE} Characteristics (Typical)




V_{CE(sat)}-I_B Characteristics (Typical)




I_c-V_{BE} Temperature Characteristics (Typical)




h_{FE}-I_c Characteristics (Typical)




h_{FE}-I_c Temperature Characteristics (Typical)




θ_{j-a}-t Characteristics



f_r-I_E Characteristics (Typical)



Safe Operating Area (Single Pulse)



P_c-T_a Derating

