

C4532X7S2A475M230KB

Applications



Commercial Grade



Please refer to Part No. CGA8N3X7S2A475M230KB for automotive use.


Feature

Mid

Mid Voltage (100 to 630V)

Series

C4532 [EIA CC1812]




Size	
Length(L)	4.50mm +/-0.40mm
Width(W)	3.20mm +/-0.40mm
Thickness(T)	2.30mm +/-0.20mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	

Electrical Characteristics	
Capacitance	4.7uF +/-20%
Rated Voltage	100Vdc
Temperature Characteristic	X7S(+/-22%)
Dissipation Factor	5% Max.
Insulation Resistance	106MΩ Min.


Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	500 Pcs Min.

C4532X7S2A475M230KB


Characteristic Graphs




C4532X7S2A475M230KB




C4532X7S2A475M230KB




C4532X7S2A475M230KB



C4532X7S2A475M230KB



C4532X7S2A475M230KB(DC Bias = 0V) C4532X7S2A475M230KB(DC Bias = 50V)



C4532X7S2A475M230KB(100kHz) C4532X7S2A475M230KB(500kHz)
C4532X7S2A475M230KB(1MHz)