THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-09-002944	20MAR2009	CR	SB


1. HOUSING: PCT, UL94V-0, COLOR: BLACK
   POSTS: PHOSPHOR BRONZE.

2. GOLD FLASH OVER
   PALLADIUM-NICKEL PLATE, 0.00076 [.000030] MIN TOTAL ON MATING AREA,
   0.00254 [.000100] MIN TIN PLATE ON SOLDER END, ALL OVER
   0.00127 [.000050] MIN NICKEL UNDERPLATE ON ENTIRE POST.
   OR
   0.00076 [.000030] MIN GOLD PLATE ON MATING AREA,
   0.00254 [.000100] MIN TIN PLATE ON SOLDER END, ALL OVER
   0.00127 [.000050] MIN NICKEL UNDERPLATE ON ENTIRE POST.


3. DATUMS S & T TO BE ESTABLISHED BY CUSTOMER.


4. ALTERNATE LOCATION/ORIENTATION FOR POSITION #1 INDICATOR.





RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)





SECTION U-U

35.56 [1.400]	14	37.59 [1.480]	43.08 [1.696]	45.72 [1.800]	30	1888871-1
E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13[.005]
4 PLC ± -
ANGLES ± -

MATERIAL 1

FINISH 2

DWN B. MCMASTER 30JAN07
CHK S.BOLASH 30JAN07
APVD S. BOLASH 30JAN07
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

Tyco Electronics
Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME HEADER ASSEMBLY, RIGHT ANGLE, LOW PROFILE, IDC

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-1888871	—

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV C

Downloaded from Arrow.com.