



Introducing EET-G-4 Thermal Transfer Labels

EET-G4 labels from Tyco Electronics were designed for thermal transfer printers using yellow woven polyamide with a permanent acrylic adhesive for application on irregular surfaces. The polyamide material can be used for wire and cable harness identification. Labels resist harsh chemical environments and are lightweight.

EET-G-4 Thermal Transfer Labels



KEY FEATURES

- Pressure sensitive acrylic label
- Resistant to harsh chemicals
- Lightweight label
- Designed for use with thermal transfer printers
- Adheres well to rounded, flexible and textured surfaces
- Strong adhesion on lightly oiled or low-surface energy surfaces

APPLICATIONS

- Aerospace and defense wire and cable identification
- Industrial & commercial wire and cable identification
- Chemical container identification

TEMPERATURE RATING

- Operating Temp: 0°C to +70°C, +32°F to +158 °F

SPECIFICATIONS AND CERTIFICATIONS

- Tyco Electronics Technical Data Sheet - TTDS-016
- Mark Permanence test: MIL-STD-202; method 215
- Eraser Rub test: MIL-M-81531

PRINTER INFORMATION


Tyco Electronics Printer: TE3112 (thermal transfer)
TE3124 (thermal transfer)
TE312M (thermal transfer)

Tyco Electronics Ribbons: 1330-3300-10 (Thermal transfer ribbon for the indicated printers is available in different sizes)

ORDERING INFORMATION

Product	Label Height		Label Width		Web width		Labels	Package
	mm	inches	mm	inches	mm	inches	across	quantity
EET-0615G-4	6.35	0.25	15.00	0.591	105.00	4.134	6	10000
EET-0818G-4	8.00	0.315	18.00	0.709	105.00	4.134	4	10000
EET-0820G-4	8.00	0.315	20.00	0.787	105.00	4.134	4	10000
EET-0825G-4	8.00	0.315	25.00	0.984	85.00	3.346	3	10000
EET-0920G-4	9.00	0.354	20.00	0.787	105.00	4.134	4	10000
EET-1325G-4	12.70	0.50	25.40	1.000	85.00	3.346	3	10000

Note: Die cut in roll format, inner-wound, inner diameter 76.20mm/3.0in.



Tyco Electronics Technical Support Center

USA: +1 (800) 522-6752
Canada: +1 (905) 470-4425
Central America & Mexico: +52 (0) 55-1106-0814
South America: +55 (0) 11-2103-6000
Germany: +49 (0) 6251-133-1999
UK: +44 (0) 8706-080208
France: +33 (0) 1-3420-8686
Netherlands: +31 (0) 73-6246-999
China: +86 (0) 400-820-6015

www.tycoelectronics.com

© 2010 Tyco Electronics Corporation. All Rights Reserved.
9-1773456-7 CIS PDF MS 4/2010
TE logo and Tyco Electronics are trademarks.

 **Tyco Electronics**
Our commitment. Your advantage.

While Tyco Electronics has made every reasonable effort to ensure the accuracy of the information in this catalog, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult Tyco Electronics for the latest dimensions and design specifications.