NOTES:


1. MATERIALS AND FINISHES:
   HD-BNC STR CRIMP PLUG - 34-1017-300
   1.0/2.3 PUSH-PULL CRIMP PLUG - 282137-75
   CABLE - BELDEN 1694A

2. ELECTRICAL:
   A. IMPEDANCE: 75 OHM


3. PACKAGING:
   A. QUANTITY: SINGLE PACK
   B. MARKING: BAG TO BE MARKED
   "AMPHENOL RF, 95-850-157XXXX, AND DATE CODE"

THIRD ANGLE PROJ.

REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	5/15/15	50350	NR/BCG



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH "L" IN INCHES [METERS]
95-850-157-006	-	6.00 [0.152]
	95-850-157M025	9.84 [0.250]
95-850-157-012	-	12.00 [0.305]
95-850-157-018	-	18.00 [0.457]
-	95-850-157M050	19.69 [0.500]
95-850-157-024	-	24.00 [0.610]
-	95-850-157M075	29.53 [0.750]
95-850-157-036		36.00 [0.914]
-	95-850-157M100	39.37 [1.000]
95-850-157-048	-	48.00 [1.219]
-	95-850-157M125	49.21 [1.250]
-	95-850-157M150	59.06 [1.500]
95-850-157-060	-	60.00 [1.524]
95-850-157-072	-	72.00 [1.829]
-	95-850-157M200	78.74 [2.000]
-	95-850-157M300	118.11 [3.000]
95-850-157-120	-	120.00 [3.048]
95-850-157-180	-	180.00 [4.572]
	95-850-157M500	196.85 [5.000]
95-850-157-300		300.00 [7.620]
-	95-850-157M10L	393.70 [10.000]
95-850-157L050	-	600.00 [15.240]
-	95-850-157M20L	787.40 [20.000]
95-850-157L075	-	900.00 [22.860]
-	95-850-157M30L	1181.10 [30.000]
95-850-157L100	-	1200.00 [30.480]



SCALE 0.500

DESIGN REQUIREMENTS:

- [X] FREQUENCY DC TO 4 GHz
- [ ] VSWR: _____ MAX
- [ ] INS. LOSS _____ dB MIN
- [X] CONTINUITY
- [X] HI-POT : 500 VRMS
- [ ] OTHER

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
2 PLACE DECIMAL ±.015 (0,381 mm) | 3 PLACE DECIMAL ±.005 (0,127 mm) | ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL: SEE NOTES

REFERENCE: EAR # 6515

CONFIGURATION LEVEL: In Work

FINISH

DRAWN	KARTHIK R	DATE 09-Dec-14
ENGINEER	KARTHIK R	DATE 09-Dec-14
APPROVED	K. CAPOZZI	DATE 5/7/15
CAD FILE		

TITLE: HD-BNC STR CRIMP PLUG TO 1.0/2.3 PUSH-PULL CRIMP PLUG, USING BELDEN 1694A CABLE, VARIOUS LENGTH

SCALE: 2.5:1.0 | SHEET 2 OF 2

DWG SIZE: B | REV: A

Amphenol RF
www.amphenolrf.com

DRAWING NO.95-850-157XXXX
ITEM NO.95-850-157XXXX
PART NO.95-850-157XXXX

Downloaded from Arrow.com.