




Color: ■ black



Dimensions in mm




Plate thickness: 1 ... 3 mm  
Cutout tolerance: + 0.1 mm

Please note!

## Mounting accessories WINSTA® MIDI 2-pole

When using the mounting accessories from the WINSTA® MIDI product line, zero-defect installation is guaranteed. An extensive range of accessories complements the WINSTA® product line from WAGO. The WINSTA® MIDI Pluggable Connection System with Push-in CAGE CLAMP® spring pressure connection technology facilitates precise electrification. Due to the built-in test slot, connections can be checked even when they are plugged in. This saves time, labor, and money.

Lower costs through fast commissioning and elimination of service expenses – solutions from WINSTA® MIDI

The WINSTA® Pluggable Connection System allows pluggable electrical installation. This saves time, lowers costs, and reduces the need for servicing. Now you can also lower installation expenses without compromising quality and safety: with protection against mismatching reduces the need for servicing and prevents unnecessary downtime.

- simple circuits
- convenient installation and commissioning

## Notes

## Note

The snap-in connectors must be relieved of tensile and transverse forces. A surface finish can influence the edge radius of the cutouts. This may affect the snap-in socket fit, so ensure an adequate fit before use. In addition, the punched edge should be on the inside for punched cutouts. The wings of the snap-in connectors must not be mechanically stressed for a long period before use (e.g., due to a pre-locking position).

## Connection data

## Connection 1

Pole number	2
-------------	---

## Physical data

Width	25.8 mm / 1.016 inches
Height	18.5 mm / 0.728 inches
Depth	38.75 mm / 1.526 inches

## Mechanical data

Housing sheet thickness	1 ... 3 mm / 0.039 ... 0.118 inches
Mounting type	Snap-in flange
Suitable	for socket and plug

## Material data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	black
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	VO
Fire load	0.076 MJ
Weight	2.7 g

**Environmental requirements**

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

**Commercial data**

Product Group	20 (Winsta)
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821261162
Customs tariff number	39269097900

**Product Classification**

UNSPSC	39121402
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 8.0	EC002863
ECCN	NO US CLASSIFICATION

**Environmental Product Compliance**

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

**Approvals / Certificates****General approvals****Declarations of conformity and manufacturer's declarations**

Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 61535	71-123228
CCA DEKRA Certification B.V.	IEC 61535	NL-84761

**Approval**   **Standard**   **Certificate Name**

EU-Declaration of Conformity	-	-
		WAGO GmbH & Co. KG

**Approvals for marine applications**

Approval	Standard	Certificate Name
ABS American Bureau of Shipping	-	24-0095977-PDA
DNV GL Det Norske Veritas, Germanischer Lloyd	-	TAE00001Z6
LR Lloyds Register	IEC 61984	LR22429487TA

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product  
Compliance 770-317



## Documentation

#### Bid Text

770-317 19.02.2019 xml 2.57 KB



770-317 02.12.2014 doc 23.00 KB



## CAD/CAE-Data

#### CAD data

2D/3D Models 770-317



#### CAE data

WSCAD Universe  
770-317



ZUKEN Portal 770-317



## 1 Compatible Products

### 1.1 Optional Accessories

#### 1.1.1 Locking system

##### 1.1.1.1 Locking system



**Item No.: 770-140**

Locking lever; for sockets and plugs; for  
tool operation; gray

## Installation Notes

### Installation



Insert the socket or plug into the frame  
(observe the "TOP" marking on the frame!), then snap the assembled unit into  
the cutout.

Snap the assembled unit into the cutout.