

Part Number : 1200868099
Product Description : Nano-Change (M8) Single-Ended Cordset, 5 Poles, B-Coded, Female (Straight) to Pigtail, 0.25mm² Black PVC Cable, 2.0m (6.56') Length
Series Number : 120086
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 405000E02M020

Documents and Resources

Drawings

1200868099_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)6375-DC (05 Nov 2025) SCIP:011eeb9e-cbd1-4d9f-b635-2a3db38901ed
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 5 Poles, B-Coded, Female (Straight) to Pigtail, 0.25mm² Black PVC Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	883906727338

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	5.30mm (.209")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail

Downloaded from Arrow.com.

Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	87.500/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	24

Downloaded from Arrow.com.