



CFM25S SERIES 25 WATT OPEN FRAME AC-DC MODULES

Features

- Universal Input Range 90~264Vac
- High Efficiency up to 87%
- 2"x 1.1" Open Frame Compact Size
- Class II
- No Load Input Power < 0.1W
- Approval IEC/EN/UL 62368-1 Ed 3.0
- Approval IEC/EN 60335-1
- Approval EN 55032 Class B and CISPR/FCC Class B
- Operating Altitude 5000m
- Continuous Short Circuit Protection
- Over Voltage Protection
- Peak Load (2 Times of Rated Current (note7))
- Over Voltage Category OVC II & OVC III



MODEL NUMBER	OUTPUT VOLTAGE	OUTPUT CURRENT	VOLTAGE ACCURACY NOTE1	RIPPLE& NOISE NOTE2	LINE REGULATION NOTE3	LOAD REGULATION NOTE4	%EFF. (Typ.) NOTE5
CFM25S050	5 V	4.0 A	±2%	50mV	±1%	±1%	81%
CFM25S120	12 V	2.1 A	±1%	120mV	±1%	±1%	84%
CFM25S150	15 V	1.67 A	±1%	150mV	±1%	±1%	85%
CFM25S240	24 V	1.05 A	±1%	240mV	±1%	±1%	86%
CFM25S360	36 V	0.7 A	±1%	360mV	±1%	±1%	87%
CFM25S480	48 V	0.52 A	±1%	480mV	±1%	±1%	87%

Note:

1. Voltage accuracy is set at 100% full load.
2. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for ripple & noise measurement @20MHz BW.
3. Line regulation is measured from 90Vac to 264Vac with 100% full load.
4. Load regulation is measured from 10% to 100% full load.
5. Typical efficiency at 230 Vac and 100% full load at 25°C.
6. T Version wafer with JST B3B-XH/B4B-XH and mate with JST housing XH series or equivalent.
7. PL (peak load function) lasting time <10 seconds with a maximum 10% duty cycle and must add external 33uF/400V capacitor to BC+ & BC-.

PART NUMBER

Series	Number of Outputs	Nominal Output Voltage	Type	Optional
CFM25	X	XXX	-XX	XX
CFM25	S : Single	050 : 5V 120 : 12V 150 : 15V 240 : 24V 360 : 36V 480 : 48V	Blank : PCB Mount E : Encapsulated T : Wafer	Blank : None PL : Peak Load Function

Part Number Example:

CFM25S120-T: Open Frame, 25W, Single 12V_{dc} Output, Wafer



CFM25S Series

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	Safety approvals only to the AC input	All	90 120		264 370	V _{ac} V _{dc}
Operating Temperature	See Derating Curve	All	-30		70	°C
Storage Temperature		All	-30		85	°C
Operating Altitude	IEC/EN/UL 62368-1 OVC II IEC/EN 60335-1 OVC II IEC 62368-1 OVC III	All			5000 2000	m

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Voltage Range		All	100		240	V _{ac}
Input Frequency Range		All	50		60	Hz
Maximum Input Current	100% Load, V _{in} =100V _{ac}	All			0.7	A
Leakage Current		All			0.25	mA
Inrush Current	V _{in} =240V _{ac} , Cold start at 25°C	All			60	A

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Set Point	V _{in} =Nominal V _{in} , I _o =I _o max., T _c =25°C	CFM25S050 CFM25S120 CFM25S150 CFM25S240 CFM25S360 CFM25S480	4.90 11.88 14.85 23.76 35.64 47.52	5 12 15 24 36 48	5.10 12.12 15.15 24.24 36.36 48.48	V _{dc}
Operating Output Current Range	V _{in} =115V _{ac} and 230V _{ac} , T _c =25°C	CFM25S050 CFM25S120 CFM25S150 CFM25S240 CFM25S360 CFM25S480			4.0 2.1 1.67 1.05 0.7 0.52	A
Holdup Time	V _{in} =115V _{ac}	All		8		ms
Output Voltage Regulation						
Load Regulation	10% Load to full load	All			±1.0	%
Line Regulation	V _{in} =High line to low line	All			±1.0	%
Over Voltage Protection	Built-in a TVS component to clamp output voltage	CFM25S050 CFM25S120 CFM25S150 CFM25S240 CFM25S360 CFM25S480	6.45 14.3 17.1 28.5 40.9 53.2	6.8 15 18 30 43 56	7.44 16.2 18.9 31.5 45.6 59.2	V _{dc}
Output Ripple and Noise	1. Add a 0.1uF ceramic capacitor and a 10uF aluminum electrolytic capacitor to output 2. Oscilloscope is 20MHz band width 3. Ambient Temperature=25°C	CFM25S050 CFM25S120 CFM25S150 CFM25S240 CFM25S360 CFM25S480			50 120 150 240 360 480	mV



CFM25S Series

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Load Capacitance	1. $V_{in}=115V_{ac}$ and $230V_{ac}$ 2. Output is max. load 3. Ambient temperature= $25^{\circ}C$	CFM25S050			81000	μF
		CFM25S120			40900	
		CFM25S150			19800	
		CFM25S240			6600	
		CFM25S360			4000	
		CFM25S480			2170	
Efficiency	1. Input voltage is $230V_{ac}$ 2. Output is rated load 3. Ambient temperature= $25^{\circ}C$	CFM25S050		81		%
		CFM25S120		84		
		CFM25S150		85		
		CFM25S240		86		
		CFM25S360		87		
		CFM25S480		87		

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input to Output	1 Minute	All			4250	V_{ac}
Isolation Resistance	Input to output	All	100			$M\Omega$

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	Pout=max. rated power	All		65		kHz

GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	I _o =100%; T _a =25°C per MIL-HDBK-217F I _o =100%; T _a =25°C per Telcordia SR332	All	500 6000			k hours
Humidity	Non-condensing	All			93	% RH
Shock	Meet MIL-STD-810F Table 516.5, Table 516.5-I 10ms, each axis 3 times(±X、±Y、±Z axis)	All		75		g
Vibration	Meet MIL-STD-810F Table 514.5C-VIII, 15~2000Hz, X、Y、Z axis, 1 hour (each axis),. Total 3 hrs.	All		4		g
Weight		CFM25S CFM25S-E CFM25S-T		38 75 40		grams
Dimensions	Blank (PCB mount)	All	2.000x1.100x0.980Inches (50.80x27.94x24.90mm)			
	E (Encapsulated)		2.091x1.193x0.976Inches (53.10x30.30x24.80mm)			
	T (Wafer)		2.776x1.100x0.906 Inches (70.50x27.94x23.00 mm)			
Safety	Class II, IEC/EN/UL 62368-1 (Ed 3.0), IEC/EN 60335-1					
EMC Emission	EN 55032 Class B, EN 61000-3-2:2019, EN 61000-3-3:2013+A1:2019, EN 61000-6-3:2007+A1:2011+AC:2012, EN 61000-6-4:2019, 47 CFR FCC Part 15 Subpart B, Oct.2014					Class B
Conducted Disturbance	EN 55032 Class B, EN 61000-6-3:2007+A1:2011+AC:2012 Class B, 47 CFR FCC Part 15 Subpart B					Class B
Radiated Disturbance	EN 55032 Class B, EN 61000-6-3:2007+A1:2011+AC:2012 Class B, 47 CFR FCC Part 15 Subpart B					Class B
Harmonic Current Emissions	EN 61000-3-2:2019					
Voltage Fluctuations & Flicker	EN 61000-3-3:2013+A1:2019					
EMC Immunity	EN 55035, EN 61204-3:2018, EN 61000-6-1:2019, EN 61000-6-2:2019					
Electrostatic Discharge (ESD)	IEC 61000-4-2:2008, Air Discharge: ±8kV, Contact Discharge: ±4kV					Criterion A
Radio-Frequency, Continuous Radiated Disturbance	IEC 61000-4-3:2020					Criterion A
Electrical Fast Transient (EFT)	IEC 61000-4-4:2012, ±0.5kV, ±1kV, ±2kV					Criterion A





CFM25S Series

GENERAL SPECIFICATIONS





Surge	IEC 61000-4-5:2014+A1:2017, L-N: $\pm 0.5\text{kV}$, $\pm 1\text{kV}$	Criterion A
Conducted Disturbances, Induced by RF Fields	IEC 61000-4-6:2013+COR1:2015	Criterion A
Power Frequency Magnetic Field	IEC 61000-4-8:2009	Criterion A
Voltage Dips	IEC 61000-4-11:2020, Dip: 30% Reduction, Dip >95% Reduction	Criterion A
Voltage Interruptions	IEC 61000-4-11:2020, >95% Reduction	Criterion B
Application Note Link		CFM25S Series App Notes

CHARACTERISTIC CURVE

Power Derating Curve




Performance Data






CFM25S Series

CFM25S360 (Eff Vs Io)




CFM25S480 (Eff Vs Io)




MECHANICAL SPECIFICATION

CFM25SXXX



CFM25SXXX-E



PIN CONNECTION


Pin	Function
1	ACL
2	ACN
3	+Vout
4	-Vout

All Dimensions are in inches[mm]
Tolerance: Inches: X.XXX±0.02
Millimeters: X.XX±0.5




CFM25S Series

CFM25SXXX PL



CFM25SXXX-E PL




PIN CONNECTION

Pin	Function
1	ACL
2	ACN
3	+Vout
4	-Vout
5	BC+(Optional)
6	BC-(Optional)

All Dimensions are in inches[mm]
Tolerance: Inches: X.XXX±0.02
Millimeters: X.XX±0.5

CFM25SXXX-T



All Dimensions In Inches[mm]
Tolerance Inches: x.xxx= ± 0.02
Millimeters: x.xx = ± 0.5

AC Input Connector(CN1): JST B3B-XH-A(LF)(SN)(2N) or equivalent

Pin	Function	Mating Housing	Terminal
1	ACL	JST XHP-3 or equivalent	JST SXH-001T-P0.6N or equivalent
2	-		
3	ACN		

DC Output Connector(CN2): JST B4B-XH-A(LF)(SN) or equivalent

Pin	Function	Mating Housing	Terminal
1	-Vout	JST XHP-4 or equivalent	JST SXH-001T-P0.6N or equivalent
2	-Vout		
3	+Vout		
4	+Vout		

CINCON Electronics Co. Ltd.
Add: 14F, No. 306, Sec.4, Hsin Yi Rd., Taipei, Taiwan
Tel: 886-2-27086210
Fax: 886-2-27029852
E-mail: sales@cincon.com
Web: www.cincon.com