


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	

- DO-IT-YOURSELF (DIY) 4mm STACKING BANANA PLUG, SCREW ATTACHMENT
- SPECIFICATIONS:
INSULATOR BODY: POLYAMIDE (NYLON)
PLUG BODY: BRASS, NICKEL PLATED
CONTACT SPRING: BERYLLIUM COPPER ALLOY, NICKEL PLATED
- RATING:
IEC: <33 V AC / <70 V DC
VOLTAGE: 1,200 V NON-HANDHELD
CURRENT: 36 A MAX.
TEMPERATURE: -20° C TO +80° C.
- MAXIMUM WIRE SIZES:
CONDUCTOR: Ø.090 (12AWG)
INSULATION: Ø.156 (5/32")
STRIP LENGTH: .25 (6.4)



MODEL NUMBER

CT2013-#

COLOR: 0 — BLACK
2 — RED
4 — YELLOW
5 — GREEN
6 — BLUE
9 — WHITE

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
		MATERIAL		APPROVALS		DATE		TITLE DIY 4mm STACKING PLUG, SCREW ATTACHMENT	
		FINISH		DRAWN WDH		7/11/99			
NEXT ASSY		USED ON		ENGR.		SIZE A		CAGE CODE 43F45	
APPLICATION				DESIGN ACTIVITY		DWG. NO. P201300		REV. A	
						SCALE 1:1		SHEET 1 OF 1	