

8 SURFACE FINISH: 32 RMS OR BETTER;  .005 [.12].

7 RECOMMENDED SCREW: 4-20 [M3.12 x 1.27] THREAD-FORMING SCREW.
TORQUE: 6-10 IN-LB [.68-1.13 NM].


6 RECOMMENDED SCREW: 6-19 [M3.63 x 1.34] THREAD-FORMING SCREW.
TORQUE: 10-20 IN-LB [1.13-2.25 NM].

5 SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.

4. THIS RECEPTACLE MATES WITH DTM06-12S*-**** PLUG
(* = A, B, C, D KEYS; **** = ALL MODIFICATIONS).


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

DTM15-12PA
KEY: -A-




3X KEYWAY
SLEEVE RETAINER: GRAY

DTM15-12PB
KEY: -B-




3X KEYWAY
SLEEVE RETAINER: BLACK

DTM15-12PC
KEY: -C-




3X KEYWAY
SLEEVE RETAINER: GREEN


DTM15-12PD
KEY: -D-



3X KEYWAY
SLEEVE RETAINER: BROWN



RECOMMENDED PANEL
CUTOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D MEYER 24APR2002	TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK R MESSENGER 21FEB2007			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±.025 [.64mm]		APVD D MEYER 21FEB2007	NAME RECEPTACLE 12 #20 SIZE CONTACTS KEY ARRANGEMENTS A, B, C AND D 180 DEG, DTM SERIES		
		PRODUCT SPEC	SIZE A3		
MATERIAL 2		APPLICATION SPEC	CAGE CODE 111139		
FINISH		WEIGHT	DRAWING NO DTM15-12PX		
		CUSTOMER DRAWING	RESTRICTED TO		
			SCALE 3:2		
			SHEET 2 OF 2		
			REV B1		