


NOTES:
1. MATERIALS:
HOUSING:
"BLANK"=NYLON 6/6, UNFILLED UL94 V-2, COLOR: NATURAL
"210"=NYLON 6/6, UNFILLED UL94 V-0, COLOR: NATURAL
"BL"=NYLON 6/6, UNFILLED UL94 V-2, COLOR: BLACK
"400"=NYLON 6/6, UNFILLED UL94 V-0, COLOR: BLACK
TERMINALS:
BRASS
2. TERMINAL PLATING:
"BLANK"=.000035/(0.00090) MIN. REFLOWED MATTE TIN OVER
.000020/(0.00050) MIN. COPPER (PREPLATE)
(FINISH IS BRIGHT IN APPEARANCE, THICKNESS AS
APPLIED PRIOR TO REFLOW)
GS2=.000015/(0.00038) MIN. SELECT GOLD AND
.000100/(0.00254) MIN. SELECT MATTE TIN
OVER .000050/(0.00127) MIN. NICKEL OVERALL
GS=.000030/(0.00076) MIN. SELECT GOLD AND
.000100/(0.00254) MIN. SELECT MATTE TIN
OVER .000050/(0.00127) MIN. NICKEL OVERALL
S=.000100/(0.00254) MIN. BRIGHT TIN OVER
.000050/(0.00127) MIN. NICKEL
MS=.000100/(0.00254) MIN. MATTE TIN OVER
.000050/(0.00127) MIN. NICKEL
3. PRODUCT SPECIFICATION: PS-5556-001
4. PACKAGING: TRAY PACKED PER PK-5566-002
5. PART MATES WITH MINI-FIT JR. RECEPTACLE NO. 5557
46994, MINI FIT SIGMA/TPA2 NO.200453.
6. PART IS NOT DESIGNED FOR CURRENT SHARING.
7. PARTS ARE NOT TO BE MATED OR UN-MATED WHILE
CIRCUITS ARE LIVE.
8. PART CONFORMS TO CLASS "B" REQUIREMENTS OF
COSMETIC SPECIFICATION PS-45499-002.
9. 5 CIRCUIT PARTS HAVE PEG DESIGN B. ALL OTHER CIRCUIT
SIZES HAVE PEG DESIGN A.

10. TEXT SHOWN IS FOR REFERENCE ONLY. TEXT AND
TEXT LOCATION MAY VARY DEPENDING ON
PART NUMBER AND/OR TOOL








PEG DESIGN B
SEE NOTE 9


PEG DESIGN A
SEE NOTE 9

POSITIVE LOCK

PASSIVE LOCK



2 CIRCUIT



LEGEND:


5566 - N A * * - *

CIRCUIT SIZE (04-12)




PEG AND LOCK OPTION
3=MTG. PEGS,POSITIVE LOCK
4=MTG. PEGS,PASSIVE LOCK

PLATING
(SEE NOTE 2)



HOUSING MAT'L
(SEE NOTE 1)

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
	DIMENSION UNITS		SCALE								CURRENT REV DESC:									
	IN/MM		4:1																	
	GENERAL TOLERANCES (UNLESS SPECIFIED)																			
	MM		INCH																	
	4 PLACES		±				±		EC NO: 806008											
	3 PLACES		±				± 0.015		DRWN: JERRYW8 2024/11/27											
	2 PLACES		±		0.38		± 0.02		CHK'D: XQZHANG 2024/12/09											
	1 PLACE		±		0.5		±		APPR: XQZHANG 2024/12/09											
	0 PLACES		±				±		INITIAL REVISION:											
	ANGULAR TOL		±		0.5 °				DRWN: KSS 1989/02/19											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										APPR: FSMITH 2012/05/06										
THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER										
		C-SIZE		5566		SEE TABLE		GENERAL MARKET		1 OF 3										

molex										VERT HDR ASSY W/ PEGS MINIFIT JR SR									
PRODUCT CUSTOMER DRAWING																			
DOCUMENT NUMBER										DOC TYPE		DOC PART		REVISION					
55660001-SD										PSD		000		B1					



POLARIZATION



SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
		IN/MM		4:1													
= 0		GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 806008 DRWN: JERRYW8 2024/11/27 CHK'D: XQZHANG 2024/12/09 APPR: XQZHANG 2024/12/09				VERT HDR ASSY W/ PEGS MINIFIT JR SR							
= 0																	
= 0				MM		INCH											
= 0		4 PLACES ±		±		DRWN: JERRYW8 2024/11/27											
= 0		3 PLACES ±		±		0.015		CHK'D: XQZHANG 2024/12/09									
= 0		2 PLACES ±		0.38		± 0.02		APPR: XQZHANG 2024/12/09									
= 0		1 PLACE ±		0.5		±		INITIAL REVISION:									
= 0		0 PLACES ±		±		DRWN: KSS 1989/02/19											
= 0		ANGULAR TOL		± 0.5 °		APPR: FSMITH 2012/05/06											
= 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
= 0										C-SIZE		5566		SEE TABLE		GENERAL MARKET	

