

NYC008-6JG

Sensitive Gate Silicon Controlled Rectifiers

Reverse Blocking Thyristors

PNPN devices designed for high volume, line-powered consumer applications such as relay and lamp drivers, small motor controls, gate drivers for larger thyristors, and sensing and detection circuits. Supplied in an inexpensive plastic TO-226AA package which is readily adaptable for use in automatic insertion equipment.

Features

- Sensitive Gate Allows Triggering by Microcontrollers and Other Logic Circuits
- Blocking Voltage to 600 V
- On-State Current Rating of 0.8 A RMS at 80°C
- High Surge Current Capability – 10 A
- Minimum and Maximum Values of IGT, VGT and IH Specified for Ease of Design
- Immunity to dV/dt – 50 V/ μ sec Minimum at 110°C
- Glass-Passivated Surface for Reliability and Uniformity
- These are Pb-Free Devices




ON Semiconductor®

<http://onsemi.com>


SCRs
0.8 A RMS
600 V



TO-92
CASE 29
STYLE 10




STRAIGHT LEAD
BULK PACK



BENT LEAD
TAPE & REEL
AMMO PACK

MARKING DIAGRAM



A = Assembly Location
Y = Year
WW = Work Week
■ = Pb-Free Package
(Note: Microdot may be in either location)

PIN ASSIGNMENT

| | PIN ASSIGNMENT |
|---|----------------|
| 1 | Cathode |
| 2 | Gate |
| 3 | Anode |

ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

| Rating | Symbol | Value | Unit |
|---|--|------------|----------------------|
| Peak Repetitive Off-State Voltage (Notes 1 and 2) ($T_J = -40$ to 110°C , Sine Wave, 50 to 60 Hz; $R_{GK} = 1\text{ k}\Omega$) | V_{DRM} , V_{RRM} | 600 | V |
| On-State RMS Current, ($T_C = 80^\circ\text{C}$) 180° Conduction Angles | $I_{\text{T(RMS)}}$ | 0.8 | A |
| Peak Non-Repetitive Surge Current, (1/2 Cycle, Sine Wave, 60 Hz, $T_J = 25^\circ\text{C}$) | I_{TSM} | 10 | A |
| Circuit Fusing Consideration, ($t = 8.3\text{ ms}$) | I^2t | 0.415 | A^2s |
| Forward Peak Gate Power, ($T_A = 25^\circ\text{C}$, Pulse Width $\leq 1.0\text{ }\mu\text{s}$) | P_{GM} | 0.1 | W |
| Forward Average Gate Power, ($T_A = 25^\circ\text{C}$, $t = 8.3\text{ ms}$) | $P_{\text{G(AV)}}$ | 0.10 | W |
| Forward Peak Gate Current, ($T_A = 25^\circ\text{C}$, Pulse Width $\leq 1.0\text{ }\mu\text{s}$) | I_{GM} | 1.0 | A |
| Reverse Peak Gate Voltage, ($T_A = 25^\circ\text{C}$, Pulse Width $\leq 1.0\text{ }\mu\text{s}$) | V_{GRM} | 5.0 | V |
| Operating Junction Temperature Range @ Rate V_{RRM} and V_{DRM} | T_J | -40 to 110 | $^\circ\text{C}$ |
| Storage Temperature Range | T_{stg} | -40 to 150 | $^\circ\text{C}$ |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

- V_{DRM} and V_{RRM} for all types can be applied on a continuous basis. Ratings apply for zero or negative gate voltage; however, positive gate voltage shall not be applied concurrent with negative potential on the anode. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.
- See ordering information for exact device number options.

THERMAL CHARACTERISTICS

| Characteristic | Symbol | Max | Unit |
|---|--|-----------|--------------------|
| Thermal Resistance, Junction-to-Case Junction-to-Ambient | $R_{\theta\text{JC}}$ $R_{\theta\text{JA}}$ | 75 200 | $^\circ\text{C/W}$ |
| Lead Solder Temperature ($< 1/16''$ from case, 10 secs max) | T_L | 260 | $^\circ\text{C}$ |

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

| Characteristic | Symbol | Min | Max | Unit |
|----------------|--------|-----|-----|------|
|----------------|--------|-----|-----|------|

OFF CHARACTERISTICS

| | | | | |
|---|-------------------------------------|--------|-----------|---------------|
| Peak Repetitive Forward or Reverse Blocking Current (Note 3) ($V_D = \text{Rated } V_{\text{DRM}}$ and V_{RRM} ; $R_{GK} = 1\text{ k}\Omega$) | I_{DRM} , I_{RRM} | - - | 10 100 | μA |
| | | | | |
| | | | | |

ON CHARACTERISTICS

| | | | | |
|---|-----------------|--------|------------|---------------|
| Peak Forward On-State Voltage* ($I_{\text{TM}} = 1.0\text{ A}$ Peak @ $T_A = 25^\circ\text{C}$) | V_{TM} | - | 1.7 | V |
| Gate Trigger Current (Note 4) $T_C = 25^\circ\text{C}$ ($V_{\text{AK}} = 7.0\text{ Vdc}$, $R_L = 100\text{ }\Omega$) | I_{GT} | - | 200 | μA |
| Holding Current (Note 3) $T_C = 25^\circ\text{C}$ ($V_{\text{AK}} = 7.0\text{ Vdc}$, Initiating Current = 20 mA, $R_{GK} = 1\text{ k}\Omega$) $T_C = -40^\circ\text{C}$ | I_{H} | - - | 5.0 10 | mA |
| Latch Current (Note 4) $T_C = 25^\circ\text{C}$ ($V_{\text{AK}} = 7.0\text{ V}$, $I_{\text{g}} = 200\text{ }\mu\text{A}$) $T_C = -40^\circ\text{C}$ | I_{L} | - - | 10 15 | mA |
| Gate Trigger Voltage (Note 4) $T_C = 25^\circ\text{C}$ ($V_{\text{AK}} = 7.0\text{ Vdc}$, $R_L = 100\text{ }\Omega$) $T_C = -40^\circ\text{C}$ | V_{GT} | - - | 0.8 1.2 | V |

DYNAMIC CHARACTERISTICS

| | | | | |
|--|---------|----|----|------------------------|
| Critical Rate of Rise of Off-State Voltage ($V_D = \text{Rated } V_{\text{DRM}}$, Exponential Waveform, $R_{GK} = 1\text{ k}\Omega$, $T_J = 110^\circ\text{C}$) | dV/dt | 50 | - | $\text{V}/\mu\text{s}$ |
| Critical Rate of Rise of On-State Current ($I_{\text{PK}} = 20\text{ A}$; $P_w = 10\text{ }\mu\text{sec}$; $di/dt = 1\text{ A}/\mu\text{sec}$, $I_{\text{gt}} = 20\text{ mA}$) | di/dt | - | 50 | $\text{A}/\mu\text{s}$ |

*Indicates Pulse Test: Pulse Width $\leq 1.0\text{ ms}$, Duty Cycle $\leq 1\%$.

3. $R_{GK} = 1000\text{ }\Omega$ included in measurement.

4. Does not include R_{GK} in measurement.

Voltage Current Characteristic of SCR

| Symbol | Parameter |
|-----------|---|
| V_{DRM} | Peak Repetitive Off State Forward Voltage |
| I_{DRM} | Peak Forward Blocking Current |
| V_{RRM} | Peak Repetitive Off State Reverse Voltage |
| I_{RRM} | Peak Reverse Blocking Current |
| V_{TM} | Peak on State Voltage |
| I_H | Holding Current |





Figure 1. Typical Gate Trigger Current versus Junction Temperature




Figure 2. Typical Gate Trigger Voltage versus Junction Temperature




Figure 3. Typical Holding Current versus Junction Temperature




Figure 4. Typical Latching Current versus Junction Temperature




Figure 5. Typical RMS Current Derating




Figure 6. Typical On-State Characteristics

NYC008-6JG

ORDERING INFORMATION

| Device | Package Code | Shipping [†] |
|----------------|-----------------------------|-----------------------|
| NYC008-6JG | TO-92 (TO-226) (Pb-Free) | 5000 Units / Box |
| NYC008-6JRLRAG | | 2000 / Tape & Reel |
| NYC008-6JRLREG | | |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

TO-92 EIA RADIAL TAPE IN BOX OR ON REEL




Figure 7. Device Positioning on Tape


| Symbol | Item | Specification | | | |
|--------|--------------------------------------|---------------|---------|------------|------|
| | | Inches | | Millimeter | |
| | | Min | Max | Min | Max |
| D | Tape Feedhole Diameter | 0.1496 | 0.1653 | 3.8 | 4.2 |
| D2 | Component Lead Thickness Dimension | 0.015 | 0.020 | 0.38 | 0.51 |
| F1, F2 | Component Lead Pitch | 0.0945 | 0.110 | 2.4 | 2.8 |
| H | Bottom of Component to Seating Plane | .059 | .156 | 1.5 | 4.0 |
| H1 | Feedhole Location | 0.3346 | 0.3741 | 8.5 | 9.5 |
| H2A | Deflection Left or Right | 0 | 0.039 | 0 | 1.0 |
| H2B | Deflection Front or Rear | 0 | 0.051 | 0 | 1.0 |
| H4 | Feedhole to Bottom of Component | 0.7086 | 0.768 | 18 | 19.5 |
| H5 | Feedhole to Seating Plane | 0.610 | 0.649 | 15.5 | 16.5 |
| L | Defective Unit Clipped Dimension | 0.3346 | 0.433 | 8.5 | 11 |
| L1 | Lead Wire Enclosure | 0.09842 | — | 2.5 | — |
| P | Feedhole Pitch | 0.4921 | 0.5079 | 12.5 | 12.9 |
| P1 | Feedhole Center to Center Lead | 0.2342 | 0.2658 | 5.95 | 6.75 |
| P2 | First Lead Spacing Dimension | 0.1397 | 0.1556 | 3.55 | 3.95 |
| T | Adhesive Tape Thickness | 0.06 | 0.08 | 0.15 | 0.20 |
| T1 | Overall Taped Package Thickness | — | 0.0567 | — | 1.44 |
| T2 | Carrier Strip Thickness | 0.014 | 0.027 | 0.35 | 0.65 |
| W | Carrier Strip Width | 0.6889 | 0.7481 | 17.5 | 19 |
| W1 | Adhesive Tape Width | 0.2165 | 0.2841 | 5.5 | 6.3 |
| W2 | Adhesive Tape Position | .0059 | 0.01968 | .15 | 0.5 |

NOTES:


1. Maximum alignment deviation between leads not to be greater than 0.2 mm.
2. Defective components shall be clipped from the carrier tape such that the remaining protrusion (L) does not exceed a maximum of 11 mm.
3. Component lead to tape adhesion must meet the pull test requirements.
4. Maximum non-cumulative variation between tape feed holes shall not exceed 1 mm in 20 pitches.
5. Hold down tape not to extend beyond the edge(s) of carrier tape and there shall be no exposure of adhesive.
6. No more than 1 consecutive missing component is permitted.
7. A tape trailer and leader, having at least three feed holes is required before the first and after the last component.
8. Splices will not interfere with the sprocket feed holes.

PACKAGE DIMENSIONS

TO-92 (TO-226)
CASE 29-11
ISSUE AM



STRAIGHT LEAD
BULK PACK




SECTION X-X


NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

| DIM | INCHES | | MILLIMETERS | |
|-----|--------|-------|-------------|-------|
| | MIN | MAX | MIN | MAX |
| A | 0.175 | 0.205 | 4.45 | 5.20 |
| B | 0.170 | 0.210 | 4.32 | 5.33 |
| C | 0.125 | 0.165 | 3.18 | 4.19 |
| D | 0.016 | 0.021 | 0.407 | 0.533 |
| G | 0.045 | 0.055 | 1.15 | 1.39 |
| H | 0.095 | 0.105 | 2.42 | 2.66 |
| J | 0.015 | 0.020 | 0.39 | 0.50 |
| K | 0.500 | --- | 12.70 | --- |
| L | 0.250 | --- | 6.35 | --- |
| N | 0.080 | 0.105 | 2.04 | 2.66 |
| P | --- | 0.100 | --- | 2.54 |
| R | 0.115 | --- | 2.93 | --- |
| V | 0.135 | --- | 3.43 | --- |



BENT LEAD
TAPE & REEL
AMMO PACK



SECTION X-X


NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

| DIM | MILLIMETERS | |
|-----|-------------|------|
| | MIN | MAX |
| A | 4.45 | 5.20 |
| B | 4.32 | 5.33 |
| C | 3.18 | 4.19 |
| D | 0.40 | 0.54 |
| G | 2.40 | 2.80 |
| J | 0.39 | 0.50 |
| K | 12.70 | --- |
| N | 2.04 | 2.66 |
| P | 1.50 | 4.00 |
| R | 2.93 | --- |
| V | 3.43 | --- |

STYLE 10:

1. CATHODE
2. GATE
3. ANODE

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative