
Your Expert Partner for **Human Machine Interfaces**

Actuator

704.101.018



https://www.eao.com/component/704.101.018/en/...

Downloaded from Arrow.com.

Your product:



704.101.018
Actuator

FRONT

Front dimension:	Ø 35 mm
Front form:	Round
Front bezel colour:	Nature
Front bezel material:	Aluminium

MOUNTING

Design:	Flush
Mounting cut-out:	Ø 30.5 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lever colour:	Black
Lever bar colour:	Black
Lever material:	plastic
Lever shape:	long

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the “Standards for low-voltage switching devices” DIN EN 60947-1

MECHANICAL CHARACTERISTICS

Switching action:	Rest - Maintained
Switching positions:	2 positions

Downloaded from Arrow.com.

Switching angle:	90° right / -45° ... +45°
Mechanical lifetime:	≤2.5 Mil. cycles of operation
Weight:	0.049 kg

AMBIENT CONDITION

IP Protection:	IP65 front side
Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C


CERTIFICATE

REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER

Short Description:	Actuator, Ø 30.5 mm, Ø 35 mm, non illuminative, Black, long, Round, Nature, Aluminium, anodised, Rest - Maintained
Hints:	Max. 3 switching elements can be clipped on
max. number of switching elements:	3

Switching positions:




Wiring diagrams:




Mounting cut-outs:

Downloaded from Arrow.com.



A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Dimension drawings:



A = Screw terminal

Downloaded from Arrow.com.