

# C3216CH2J151J060AA

TDK Item Description : C3216CH2J151JT\*\*\*\*




## Application & Main Feature

Commercial Grade ( Mid Voltage (100 to 630V) )

## Series

C3216 [EIA CC1206]



## Dimensions

L 3.20mm +/-0.2mm  
W 1.60mm +/-0.2mm  
T 0.60mm +/-0.15mm  
B 0.20mm Min.  
G 1.00mm Min.

## Temperature Characteristic

CH (-25 to 85 degC 0+/-60ppm/degC)

## Rated Voltage

2J (630Vdc)

## Capacitance

150pF

## Capacitance Tolerance

J (+/-5%)

## O Factor

1000 Min.


## Insulation Resistance

10Gohm Min.


## AEC-Q200

Not Applicable


|Z|, ESR vs. Freq. Characteristics




DC Bias Characteristic



Cap. vs. Freq. Characteristic



Temperature Characteristics



All specifications are subject to change without notice.

January 3, 2016