


643265 -7 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



643265 -7

Active

MTA, CST -100 II, MT -6 and SL Connectors and Headers

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- ? MTA-100 Connectors
- ? Number of Positions = 9
- ? Mating Type = Header
- ? Wire -to -Board Application
- ? 2.54 mm Contact Centerline Spacing

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(84\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .0...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Mating Products \(84\)](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = MTA -100 Connectors
- ? [Number of Positions](#) = 9
- ? [Mating Type](#) = Header
- ? [PCB Mount Angle](#) = Vertical
- ? PCB Retention Feature = No
- ? [Mating Polarization](#) = Without
- ? [Mating Connector Lock](#) = With
- ? [Four Points of Contact](#) = Without
- ? [Shrouded](#) = No
- ? [Mounting Ears](#) = Without
- ? Mating Connector Lock Type = Friction Lock
- ? PCB Thickness (mm [in]) = 1.60 [0.063]
- ? Post Size (mm [in]) = 0.64 [.025]

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Electrical Characteristics:

- ? Voltage Rating (VAC) = 250

Termination Related Features:

- ? [Solder Tail Contact Plating](#) = Tin

Body Related Features:

- ? [Narrow](#) = No
- ? [Post Number\(s\) Omitted](#) = 6

Contact Related Features:

- ? [Contact Centerline Spacing \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Contact Shape](#) = Square
- ? [Contact Mating Area Plating Material](#) = Tin
- ? [Contact Material](#) = Copper Alloy

Housing Related Features:

- ? Housing Color = Natural
- ? Housing Flammability Rating = UL 94V -0
- ? Housing Material = Thermoplastic Polyester

Configuration Related Features:

- ? [Backwall/Post Interruption\(s\)](#) = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Operation/Application:

- ? [Application](#) = Wire -to -Board

Other:

- ? Brand = AMP