


REVISIONS	
A	0017273
KSR	
21 NOV05	

--	--


--	--

--	--

3



DRAWN
ER


ROLLER LEVER MAY BE POSITIVELY LOCKED AT INTERVALS OF APPROXIMATELY 0.2° WITHIN A RANGE OF 225° (1238 POSITIONS)



NOTE

- 1 - FURNISHED UNASSEMBLED
 2 - ROLLER LEVER BRACKET ASSEMBLY MAY BE SET AT ANY POSITION AROUND AXIS OF PLUNGER
 3 - SWITCH CAVITY FULLY POTTED
 4 - SEAL RATING: NEMA 1, 3, 4, 12, 13 IP 56

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION 
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — — 14-26 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE — — — — 10 OZ MIN	L270 10A 125, <u>250</u> OR 480 VAC 2A 600 VAC 1/8HP 125 VAC, 1/4HP <u>250</u> VAC 1/2A 125 VDC, 1/4A 250 VDC  1.5A, 240 Vac	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
PRETRAVEL — — — — .188 MAX		ONE PLACE (.0) ±.030
DIFFERENTIAL TRAVEL — — — — .006 MAX		TWO PLACE (.00) ±.015
OVERTRAVEL — — — — .219 MIN		THREE PLACE (.000) ±.005
		ANGLES ±
		WEIGHT



CIRCUIT DIAGRAM

ANSI Y14.5M-1982 APPLIES