



Home> Products > Detector > Optoschmitt Sensor > Product Page

HOA6992-L51



Actual product appearance may vary.

Features

- Direct TTL interface
- Buffer or inverting logic available
- Three device output options
- Four mounting configurations
- Choice of detector aperture
- 0.125 in [3.18 mm] slot w idth
- 24.0 in [610 mm] min. 26 AWG UL 1429 wire leads

Description

The HOA698X/699X series consists of an infrared emitting diode facing an Optoschmitt detector encased in a black thermoplastic housing. Detector sw itching takes place w henever an opaque object passes through the slot betw een emitter and detector. The photodetector consists of a photodiode, amplifier, voltage regulator, Schmitt trigger and various output configurations. The user can choose from available options:(1) detector aperture, (2) mounting tab configuration, (3) detector output configuration, and (4) housing material. The HOA698X series utilizes an IR transmissive polysulfone housing w hich features smooth optical faces w ithout external aperture openings; this feature is desirable w hen aperture blockage from airborne contaminants is a possibility. The HOA699X series employs an opaque polysulfone housing w ith aperture openings for use in applications in w hich maximum rejection of ambient light is important, and situations in w hich maximum position resolution is desired. The HOA698X/699X series employs plastic molded components. For additional component information see SEP8506 and SDP8XX4. Housing material is polysulfone. Housings are soluble in chlorinated hydrocarbons and ketones. Recommended cleaning agents are methanol and isopropanol. Device Polarity: Buffer - Output is LO w hen optical path is blocked. Inverter - Output is HI w hen optical path is blocked. Wire color code and functions are: Red - IRED Anode Black - IRED Cathode Green - Detector Ground White - Detector Vcc Blue - Detector Output

Supporting Documentation

- Dimensions
- Schematics and Performance Charts
- Engineering Drawing

Product Specifications	
Series Name	Optoschmitt Sensor
Product Type	IR Switch
Output	Totem -Pole
Output Logic	Inverter
Mounting Configuration	Single Mounting Tab, Emitter Side
Package Components	Plastic
Package Color	Black
Continuous Forward Current	50 mA
Forward Voltage	1.6 V
Reverse Breakdown Voltage	3 V
Reverse Current	10 µA
Maximum Trigger Current	15 mA
Housing Material	Polysulfone, Opaque
Power Dissipation	100 mW
Operating Temperature Range	-40 °C to 70 °C [-40 °F to 158 °F]
Hysteresis (H)	0.05
Operating Supply Voltage	4.5 V to 7.0 V
Supply Voltage	7.0 Vdc
High Level Output Voltage	2.4 V minimum
High Level Supply Current	15 mA
Low Level Output Voltage	0.4 V maximum
Low Level Supply Current	15 mA
Short Circuit Output Current	-20 mA to -100 mA
Output Rise Time	70 ns
Output Fall Time	70 ns
Propagation Delay, Low-High,High-Low	5.0 µs
Duration of Output Short Vcc or Ground	1.0 second
IRED Trigger Current	15 mA
IRED Anode Color	Red
IRED Cathode Color	Black
Detector Vcc Color	White
Detector Output Color	Blue
Detector Ground Color	Green
Comment	Output is HI when incident light intensity is above the turn-on threshold level.
Availability	Global
Sensor Aperture	1,52 mm x 0,25 mm [0.060 in x 0.010 in]
Slot Width	3,18 mm [0.125 in]

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search