

Products


Documentation

Resources

My Account

Customer Support

326799 Product Details



326799

Active

AMPOWER Terminals

Always EU RoHS/ELV Compliant

 ( 

Statement of Compliance

 )

Product Highlights:

- ?

Power Generation and Distribution Application
- ?

Wire Size (AWG/CM) = 2 AWG [34 - 35<sup>2</sup>]
- ?

Wire Range = 52600 - 83700 CMA
- ?

Terminal Type = Standard
- ?

Stud Size = 3/8 [9.53]

View all Features

 | 

Find Similar Products

Live Product Chat

US Only

8:30am - 5pm ET, Mon - Fri

Quick Links

- Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

| Documentation & Additional Information                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                                                                                                                                                                                                                                                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div>Product Drawings:</div><div><div>?</div><div><div><a href="#">TERMINAL, AMPOWER, WIRE SIZE: 2 AWG</a></div><div>(PDF, English)</div></div></div></div> <div><div>Catalog Pages/Data Sheets:</div><div><div>?</div><div>None Available</div></div></div> <div><div>Product Specifications:</div><div><div>?</div><div>None Available</div></div></div> <div><div>Application Specifications:</div><div><div>?</div><div>None Available</div></div></div> <div><div>Instruction Sheets:</div><div><div>?</div><div>None Available</div></div></div> <div><div>CAD Files:</div><div><div>?</div><div>None Available</div></div></div> <div><div><a href="#">List all Documents</a></div></div> | <div><div>Additional Information:</div><div><div>?</div><div><div><a href="#">Product Line Information</a></div></div></div></div> <div><div>Related Products:</div><div><div>?</div><div><div><a href="#">Tooling</a></div></div></div></div> |

Additional Information:

?

Product Line Information

Related Products:

?

Tooling

List all Documents

| Product Features                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| (Please use the Product Drawing for all design activity)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| <div><div>Product Type Features:</div><div><div>? Terminal Type = Standard</div><div>? Stud Size = 3/8 [9.53]</div><div>? Stud Diameter (mm [in]) = 9.53 [0.375]</div><div>? Material = Copper (Annealed) per ASTM B - 75</div><div>? Body Style = Straight</div><div>? Tongue Material Thickness (mm [in]) = 2.29 [0.090]</div><div>? Finish = Tin</div><div>? Comment = Electrodeposited Tin Plate per MIL T-10727.</div></div></div> <div><div>Body Related Features:</div><div><div>? Wire Size (AWG/CM) = 2 AWG [34 - 35<sup>2</sup>]</div><div>? Wire Range (CMA) = 52,600 - 83,700</div><div>? Stud Hole Diameter (mm [in]) = 9.91 [0.390]</div><div>? Number of Holes = 2</div><div>? Barrel I.D. Min. (mm [in]) = 9.19 [0.362]</div><div>? Barrel Length = Standard</div><div>? Inspection Slot = With</div></div></div> | <div><div>Industry Standards:</div><div><div>? RoHS/ELV Compliance = RoHS compliant, ELV compliant</div><div>? Lead Free Solder Processes = Not relevant for lead free process</div><div>? RoHS/ELV Compliance History = Always was RoHS compliant</div></div></div> <div><div>Operation/Application:</div><div><div>? Application = Power Generation and Distribution</div></div></div> <div><div>Packaging Related Features:</div><div><div>? Packaging Quantity = 50</div></div></div> <div><div>Other:</div><div><div>? Brand = AMP</div></div></div> |

Body Related Features:

?

Wire Size (AWG/CM)

 = 2 AWG [34 - 35<sup>2</sup>]

?

Wire Range (CMA)

 = 52,600 - 83,700

?

Stud Hole Diameter (mm [in])

 = 9.91 [0.390]

?

Number of Holes

 = 2

?

Barrel I.D. Min. (mm [in])

 = 9.19 [0.362]

?

Barrel Length

 = Standard

?

Inspection Slot

 = With

Industry Standards:

?

RoHS/ELV Compliance

 = RoHS compliant, ELV compliant

?

Lead Free Solder Processes

 = Not relevant for lead free process

?

RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

?

Application = Power Generation and Distribution

Packaging Related Features:

?

Packaging Quantity = 50

Other:

?

Brand = AMP