



- NOTES:
- MATERIALS AND FINISHES:
BODIES, LOCK RING - BRASS, NICKEL PLATING
CONTACTS - BeCu, GOLD PLATING
INSULATORS - PTFE
GASKET - SILICONE RUBBER, RED
 - ELECTRICAL:
A. IMPEDANCE: 50 OHM
 - MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
 - PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 31-3220-1021, 1250-0161, AND DATE CODE"
 - MAX. PANEL THICKNESS=6.98mm 2 SPACES




SCALE 5.000
RECOMMENDED PANEL CUTOUT DIMENSIONS



SCALE 1.800

THIRD ANGLE PROJ.

REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
--	RELEASE TO MFG.	--	--	--
K	COD SHEET ADDED	17-Sep-14	49594	RM



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN A ARUN PRABU	DATE 10-Mar-14	TITLE BNC ADAPTER (PRESSURIZED) JACK TO JACK	Amphenol RF www.amphenolrf.com	
		ENGINEER K.CAPOZZI	DATE 10-Mar-14			
	REFERENCE: DOR 305553-51 AGILENT 1250-0161	APPROVED S.HSIEH	DATE 17-Sep-14	SCALE: 5.0:1.0	SHEET 2 OF 2	DRAWING NO. 31-3220-1021
	CONFIGURATION LEVEL: ☐ ☐ ☐	CAD FILE		DWG SIZE B	REV K	ITEM NO. 31-3220-1021
	FINISH					PART NO. 31-3220-1021